### multicomp PRO

RoHS

**Compliant** 



#### **Features**

- Universal 85V AC to 264V AC or 120V DC to 370V DC input voltage
- High power density, compact size: 3" x 2" x 1.22"
- Operating ambient temperature range: -40°C to +85°C
- Active PFC
- · High I/O isolation test voltage up to 4000V AC
- · Operating altitude up to 5000m
- Extremely low leakage current<0.1mA</li>
- Stand-by power consumption<0.3W</li>
- The base plate with conformal coating
- · Output short circuit, over-current, over-voltage, over-temperature protection
- Efficiency up to 95%
- · Installing in system of Safety Class I/II is available
- Safety according to IEC/EN/UL62368-1, IEC/EN60335-1,
- IEC/EN61558-1, GB4943-1, IEC/EN/ES60601-1

These series is one of AC-DC miniaturize open frame power supply. It features universal AC input and at the same time accepts DC input voltage, cost-effective, high efficiency, high reliability and double or reinforced insulation. These converters offer excellent EMC and safety performance, which meet IEC/EN/UL62368, GB4943, IEC/EN60335, IEC/EN61558, IEC/EN/ES60601 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home, medical, etc.

Selection Guide							
Part Number	Nominal Output Power (W)	Nominal Output Voltage and Current (Vo/Io)	Transient Output Power*10S (W)	Output Voltage Adjustable Range (V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (µF)	
MPOF120-20B12	114	12V/9.5A	141.6	11.4-12.6	94	6000	
MPOF120-20B15	114	15V/7.6A	142.5	14.3-15.8	94	5000	
MPOF120-20B24	120	24V/5A	150	22.8-25.2	95	3200	
MPOF120-20B27	119.9	27V/4.44A	149.8	25.6-28.4	95	2400	
MPOF120-20B48	120	48V/2.5A	150	45.6-50.4	94.5	1600	

Note: \*If the total output power exceeds the nominal output power, it can be maintained for a maximum of 10s. The power supply cannot exceed the transient power. When the output voltage is increased, the total output power cannot exceed the nominal output power.

Input Specifications						
Item		Operating Conditions	Min.	Тур.	Max.	Unit
Input Voltage Range	AC input		85		264	VAC
Imput voltage Range	DC input		120		370	VDC
Input Voltage Frequency			47		63	Hz
1 10 1	115VAC	5VAC			2	
Input Current	230VAC				1	A
Inrush Current	115VAC	Cold start		40		] ^
I III usii Cuiteiii	230VAC	Cold start		75		
Dower Footer	115VAC		0.98			
Power Factor	230VAC	Full Load	0.94			]
Leakage Current	240VAC		<0.1mA	; Single fa	ult<0.5mA	
Hot Plug			Unavailable			

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





### **Output Specifications**

Item	Operating Conditions		Min.	Тур.	Max.	Unit
Outrot Valtage Assument	Full load range	12V/15V		±2.0		
Output Voltage Accuracy*		24V/27V/48V		±1.0		
Line Regulation	Rated load	Rated load		±0.5		%
Load Regulation	0% - 100% load			±1.0		]
	001411	12V/15V		80	120	
Ripple & Noise*	20MHz bandwidth	24V/27V		100	150	] mV
	(peak-to-peak value)	48V		120	200	
Temperature Coefficient		'		±0.03		%/°C
Minimum Load		'	0			%
Hold-up Time			15			ms
Stand-by Power Consumption					0.3	W
Short Circuit Protection	Recovery time < 3s after the short circuit disappear.		Hiccup, continuous, self-recovery			covery
Over-current Protection			≥130% Io, hiccup, self-recovery			overy
	12V		≤16V (Output voltage turn off, re-power on for recover)			
	15V		≤25V (Output voltage turn off, re-power on for recover)			
Over-voltage Protection	24V		≤32V (Output voltage turn off, re-power on for recover)			
	27V		≤35V (Output voltage turn off, re-power on for recover)			
	48V		≤60V (Output voltage turn off, re-power on for recover)			
Over-temperature Protection		Output voltage turn off, re-power on to recovery after abnormal removed				

Note: 1. \*Output voltage accuracy: including the setting error, line regulation, load regulation;

<sup>2. \*</sup>The "Tip and barrel method" is used for ripple and noise test, output parallel 10uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to AC-DC Converter Application Notes for specific information;

<sup>3. \*</sup>For all the above test items, please refer to our company standard "AC-DC Black Box Test Specification" for specific test specifications and methods;

<sup>4. \*</sup>Except for special instructions, the above data are measured at the full operating temperature range and humidity <75%.



General Sp	ecifications						
Item		Operating Conditions		Min.	Тур.	Max.	Unit
Input - ≟				1500			
Isolation Test	Input - output	Electric strength test for 1min., leakage current <5mA		4000			VAC
	Output - 🖶			500			
1 1 0	Input - 🖶	Ambient temperature: 2	Ambient temperature: 25 ± 5°C				
Insulation Resistance	Input - output	Relative humidity: < 95%	%RH, no condensation	100			ΜΩ
resistance	Output - 🖶	Test voltage: 500V DC		100			
Operating Temp	erature			-40		+85	- °C
Storage Temper	rature			-40	] -	+85	
Operating Humi	dity	Non condensing	,	10	1	95	%RH
Storage Humidity		Non-condensing		20	]	90	/01X11
Switching Frequ	iency	Nominal output power		70		110	kHz
Power Derating		Operating temperature	+50°C to +85°C	2			//°C
		derating	-40°C to -30°C	2	]		%/ C
		Input voltage derating	85VAC - 115VAC	1			%/VAC
Safety Standard				/GB4 ES6060 <sup>2</sup> C22.2	JL62368 EN6 943-1/II 1-1(3.1 v No.6060	1558-1 EC/EN60	CAN/CSA- Edition 3/
Safety Certification				IEC/EN/UL62368-1/EN60335/ IEC61558(Pending)			
Safety Class				CLASS I			
	Input - output		2 × M0		MOPP		
Isolation level	Input - 🖶			1 × MOPP			
	Output - 🖶			1 × MOPP			
MTBF		MIL-HDBK-217F@25°C			>300	),000 h	
Warranty		Ambient temperature: <	mperature: <50°C 5 years		years		

Mechanical Specifications				
Case Material	Open frame			
Dimensions	76.2mm x 50.8mm x 31mm			
Weight 125g (Typ.)				
Cooling Method Free air convection				
Note: *Cooling method and power derating refer to typical characteristic curves.				

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro







### **Electromagnetic Compatibility (EMC)**

	CE	CISPR32/EN55032	CLASS B				
Emissions	RE	CISPR32/EN55032	2 (Category I, CLASS B, category II, CLASS A)				
	Harmonic current		IEC/EN61000-3-2 CLASS A				
	ESD	IEC/EN 61000-4-2	Contact ±6KV/Air ±8KV	Perf. Criteria A			
	RS	IEC/EN 61000-4-3	10V/m	Perf. Criteria A			
	EFT	IEC/EN 61000-4-4	±2KV	Perf. Criteria A			
Immunity	Surge	IEC/EN 61000-4-5	line to line ±2KV/line to ground ±4KV	Perf. Criteria A			
	CS	IEC/EN61000-4-6	10 Vr.m.s	Perf. Criteria A			
	Voltage dips, short interruptions and voltage variations immunity	IEC/EN61000-4-11	0%, 70%	perf. Criteria B			


Note: \*The power supply should be considered as a part of the components in the system. All EMC performance are been tested on a metal plate with a thickness of 1mm and a length of 360mm × 360mm. The power supply must be combined with the terminal equipment for electromagnetic compatibility confirmation.


#### **Product Characteristic Curve**






Note: With an AC input voltage between 85 - 115VAC and a DC input between 120 - 160VDC the output power must be derated as per the temperature derating curves.





### multicomp PRO

### **Dimensions and Recommended Layout**





THIRD A	NGLE	PROJEC	CTION



Pin	Function	Product Connector	Customer Connector	
1	AC(N)	JST B3P-VH	Housing:JST VHR	
2	NC	or equivalent	Contact:JST SVH-21T-P1.1	
3	AC(L)		or equivalent	
4, 5	-Vo	JST B4P-VH	Housing:JST VHR	
6, 7	+Vo	or equivalent	Contact:JST SVH-21T-P1.1 or equivalent	

Position	Screw Spec.	L(Recommend)	Torque(max)
1 - 4	M3	6mm	0.4N • m





#### Note:

- 1. Unit: mm[inch]
- 2. General tolerances:  $\pm 1.00[\pm 0.039]$
- 3. The layout of the device is for reference only , please refer to the actual product

#### Notes:

- 1. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 3. All index testing methods in this datasheet are based on our company corporate standards;
- 4. In order to improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

