


# MTi-2

- Miniature form factor (12x12 mm)
- Easy integration
- Development Kit available

The MTi-2 is a self-contained Vertical Reference Unit (VRU) as a 12.1 x 12.1 mm module. The Xsens optimized strapdown algorithm (AttitudeEngine™) performs high-speed dead-reckoning calculations at 1 kHz allowing accurate capture of high frequency motions. Xsens' industry-leading sensor fusion algorithm provides high accuracy and sensor auto-calibration in a cost-effective module for a wide range of (embedded) applications. It relieves users from the design, integration and maintenance of gyroscopes, accelerometers and other sensors. The MTi-2 is supported by the MT Software Suite which includes MT Manager (GUI for Windows/Linux), SDK, example codes and drivers for many platforms.



## Sensor fusion performance

Roll, Pitch	0.5 deg RMS
Yaw/Heading	unreferenced, low drift
Strapdown Integration (SDI)	Yes

## Gyroscope

Standard full range	2000 deg/s
In-run bias stability	10 deg/h
Bandwidth (-3dB)	255 Hz
Noise Density	0.007 °/s/√Hz
g-sensitivity (calibr.)	0.001 °/s/g

## Accelerometer

Standard full range	16 g
In-run bias stability	30 µg
Bandwidth (-3dB)	324 (x,y) 262 (z) Hz
Noise Density	120 µg/√Hz

## Magnetometer

Standard full range	+/- 8 G
Total RMS noise	0.5 mG
Non-linearity	0.2%
Resolution	0.25 mG

## GNSS Receiver

GNSS receiver interface	n/a
GNSS precision	n/a
RTCM input port	n/a

## Barometer

Barometer interface	n/a
---------------------	-----

## Mechanical

IP-rating	IP00
Operating Temperature	-40 to 85 °C
Casing material	PCB
Mounting orientation	No restriction, full 360° in all axes
Dimensions	12.1 x 12.1 x 2.55 mm
Connector	SMD, footprint compatible with JEDEC PLCC-28
Weight	0.6 g

## Electrical

Input voltage	2.19 to 3.6V
Power consumption (typ)	44 mW @ 3V

## Interfaces / IO

Interfaces	UART, SPI, I²C
Sync Options	Yes
Protocols	Xbus
Clock drift	10 ppm
Output Frequency	Up to 1 kHz, 100 Hz SDI
Built-in-self test	Yes

## Software Suite

GUI (Windows/Linux)	MT Manager Firmware updater, Magnetic Field Mapper
SDK (Example code)	C++, C#, python, Matlab, Nucleo, public source code
Drivers	LabVIEW, ROS, GO
Support	BASE by XSENS: online manuals, community and knowledge base

- 3D models available on request
- Available online via Digi-Key, Mouser, Farnell and local distributors