

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Drill/Driver

GSB 18V-55



Bosch's powerful entry-level 18 V impact drill with brushless motor

The most important data

Max. drilling diameter in masonry	13 mm
Max. screw diameter	10 mm
Weight excl. battery	1.1 kg

Part Number 0 601 9H5 302[> More product information](#)

Technical data

Technical data

Torque (soft/hard/max.)	28/55/- Nm
No-load speed (1st gear / 2nd gear)	0 – 460 / 0 – 1,800 rpm
Battery type	Lithium-ion
Chuck capacity, min./max.	1.5 / 13 mm
Weight excl. battery	1.1 kg
Torque settings	20+2

'Total vibration values (Drilling in metal)'

Vibration emission value ah	1.5 m/s ²
Uncertainty K	1.5 m/s ²

'Total vibration values (Impact drilling in masonry)'

Vibration emission value ah	11 m/s ²
Uncertainty K	1.5 m/s ²

Drilling diameter

Max. drilling diameter in wood	35 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in masonry	13 mm

Screw diameter

Max. screw diameter	10 mm
---------------------	-------

Noise/vibration information

Drilling in metal

Vibration emission value ah	1.5 m/s ²
Uncertainty K	1.5 m/s ²

Impact drilling in masonry

Vibration emission value ah	11 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Tough and powerful: performance of 55 Nm and 1,750 RPM for highest efficiency when working in wood, metal, and masonry
- Robust 13-mm Roehm metal chuck offers ideal power transfer for drilling and screwdriving
- Brushless motor ensures extensive tool lifetime and longer battery runtimes

