

61.194.11 ✓ ACTIVE


TE Internal #: 61-0194-011-000

Standard Circular Connectors, 5A Contact Current Rating (Max),  
Power, Brass, 23 Shell Size, 0° Alignment Keyed, Metal, Pin

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**

Contact Current Rating (Max): **5 A**

Circuit Application: **Power**

Shell Base Material: **Brass**

Circular Connector Shell Size: **23**

## Features

### Product Type Features

Sealable	No
Shell Type	Metal

### Body Features

Shell Base Material	Brass
---------------------	-------

### Contact Features

Contact Current Rating (Max)	5 A
Circular Connector Contact Type	Pin

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

### Operation/Application

Durability Rating	500 Cycles
-------------------	------------



Circuit Application

Power

## Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUN 2020 (209)  
 Candidate List Declared Against: JUN 2020 (209)  
 SVHC > Threshold:  
 Pb (1.5% in Component)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # C0-0236-000-000  
 DIGITAL CRIMPING TOOL, MID SIZE


TE Part # C0-0201-000-000  
 CRIMPING TOOL MID-SIZE

TE Part # C0-0004-000-000  
 POSITIONING INSERT FOR 2 MM CONTACTS

## Customers Also Bought



TE Part #103968-7  
2X8 MTE RCPT SR RIBBED .100CL



TE Part #825435-2  
MOD 2 PINHDR 1X02P.



TE Part #1-1879519-1  
CRGH2010 1% 137R 1W



TE Part #6-1879640-6  
H4P 26K1 0.5% 50PPM



TE Part #1-499786-2  
AMP-LATCH UNIVERSAL HEADERS




TE Part #YDTS20W25-04BAV001  
D38999: Square Flange, 25-04 insert



TE Part #YDTS24W17-06PAC001  
D38999: Jam Nut, 17-06 Insert



TE Part #CGA257N00000056000  
940 RECEPTACLE ANGLED,  
ROTATABLE, SP-READY



TE Part #3-1879635-8  
H4 787K 0.5% 15PPM



TE Part #1-223969-0  
UNV PWR MDL, GUIDE PIN LOCT PL

## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_61-0194-011-000\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_61-0194-011-000\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_61-0194-011-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### Pin 2mm 61.194.11

English