



Product data sheet

Power tools for trade & industry

Cordless Impact Driver

GDR 18V-160



The ergonomic entry-level impact driver in the 18 V category

The most important data

Battery voltage	18 V
Torque, max.	160 Nm
Screw diameter	M 6 – M 14

Part Number 0 601 9G5 104

[> More product information](#)

Technical data

Technical data

No-load speed	0-2,800 rpm
Weight excl. battery	1.02 kg
Torque, max.	160 Nm
Impact rate	0-3,600 bpm
Battery voltage	18 V
Tool holder	1/4" Hex Uni
Tool dimensions (length)	153 mm
Tool dimensions (height)	234 mm
Packaging dimensions (width x length x height)	360 x 440 x 155 mm

'Total vibration values (Tightening screws and nuts of maximum permitted size)'

Vibration emission value ah	9.5 m/s ²
Uncertainty K	1.5 m/s ²

Screw diameter

Screw diameter	M 6 – M 14
----------------	------------

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	9.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Ergonomic design provides convenient tool handling for precise working results
- High torque makes the tool powerful and easy to use even in heavy applications
- Combination of high torque and high speed supports fast working progress and efficiency

