


PF-XAL-AL (PIW) 630VDC Audio Capacitors Paper in Wax, Aluminium Foil



CAPACITANCE μF	D	L
0.01 – 0.05	15mm	34mm
0.05+ – 0.47	25mm	54mm
0.47+ -1.2	35mm	54mm
1.2+ – 3.3	45mm	95mm
3.3+ – 10.0	65mm	95mm

AMPOHM Audio Capacitors are specially designed for high performance audio systems, used in various applications. These paper in wax (PIW) capacitors are hand wound using high purity aluminium foil and have their 1.0mm diameter tinned copper leads hand solder sealed to the eyelets in the end discs. They are wax impregnated before being assembled and hermetically sealed in an aluminium housing with phenolic resin and rubber end discs, all being individually hand tested.

Custom Designs available

Type: PF-XAL-AL
Capacitance: 0.01 μF – 10.0 μF
Dissipation Factor: < 0.01@ 1KHz
Tolerance: +/- 20% up to 0.1 μF
 +/- 10% up to 5.0 μF
 +/- 5% above 5.0 μF
Rated Voltage: 630V DC
Temperature Range: -40 to +85C
Outer Foil: Line on label denotes outer foil

Marking:

	AMPOHM
	AUDIO CAPACITOR
	TYPE
	VALUE/VOLTAGE
	SPEC
	DATE CODE

Line on label denotes outer foil

Witness Innovation... Experience Technology



Registered Office: Ampohm Wound Products Ltd, Unit 1d Treburley Industrial Estate, Treburley, Launceston, Cornwall, PL15 9PU
 Tel: 01423 865641 • Fax: 01423 798246 • E-mail: sales@ampohm.co.uk • Website: www.ampohm.co.uk

Witness Innovation... Experience Technology

Registered Office: Ampohm Wound Products Ltd, Unit 1d Treburley Industrial Estate, Treburley, Launceston, Cornwall, PL15 9PU
Tel: 01423 865641 ▪ Fax: 01423 798246 ▪ E-mail: sales@ampohm.co.uk ▪ Website: www.ampohm.co.uk



Registered in England & Wales No: 5654904

VAT Registration: 874 7628 73