

Product Search Data Sheet

DLW5ATH401TQ2L


In Production RoHS REACH 0200

< List of part numbers with package codes > DLW5ATH401TQ2K DLW5ATH401TQ2L



Appearance & Shape





Applications

Automotive Usage

Powertrain/Safety

Note: This datasheet may be out of date. Please download the latest datasheet of DLW5ATH401TQ2# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DLW5ATH401TQ2%23

"#" indicates a package specification code.

DLW5ATH401TQ2B



Packaging Information

Packaging	Specifications	Standard Packing Quantity
к	330mm Embossed Tape	2500
L	180mm Embossed Tape	700
В	Bulk(Bag)	100



Features

Low profile (h=2.35mm) chip common mode choke coil. Suitable for noise suppression at DC power lines.

Features

- 1. Low profile (h=2.35mm)
- 2. Small size (5.0x3.6mm)
- 3 .Large Current Available (1.5Ato 4A)
- 4 . Operating Temperature Range -40°C to +125°C

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





DLW5ATH401TQ2L

Note: This datasheet may be out of date. Please download the latest datasheet of DLW5ATH401TQ2# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DLW5ATH401TQ2%23

"#" indicates a package specification code.



Specifications

Shape	SMD	
Size Code (in mm)	5036	
Size Code (in inch)	2014	
Length	5.0mm	
Length Tolerance	±0.3mm	
Width	3.6mm	
Width Tolerance	±0.3mm	
Thickness	2.2mm	
Thickness Tolerance	±0.15mm	
Common Mode Impedance (at 100MHz)	400Ω	
Common Mode Impedance (at 100MHz) Tolerance	(Тур.)	
Common Mode Impedance (at 10MHz)	35Ω	
Common Mode Impedance (at 10MHz) Tolerance	±25%	
Rated Current	2A	
Derating of Rated Current	Yes (Over 105°C) *For details, please check the derating diagram.	
Rated Voltage	50Vdc	
Withstanding Voltage	125Vdc	
DC Resistance(max.)	0.034Ω	
DC Resistance	0.034Ω max.	
Insulation Resistance(min.)	10ΜΩ	
Operating Temperature Range	-40°C to 125°C	
Mass(typ.)	0.14g	

Number of Circuit	1
Operating Temperature	
Range(Self-temperature rise	No
is included)	

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




DLW5ATH401TQ2L

Note: This datasheet may be out of date. Please download the latest datasheet of DLW5ATH401TQ2# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DLW5ATH401TQ2%23

"#" indicates a package specification code.







Impedance-Frequency Characteristics

In operating temperature exceeding +105°C, derating of current is necessary for DLW5ATH_TQ2 series. Please apply the derating curve shown in chart according to the operating temperature.






Derating of Rated Current



Impedance-Frequency Characteristics (Main Items)



Equivalent Circuit

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

