

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Type of product : Fillers, putties, plasters, modelling clay, Thermal interface material

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Use of the substance/mixture : Thermal interface material
Function or use category : Heat transfer agents, Fillers

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Premier Farnell plc
150 Armley Road, Leeds, LS12 2QQ
+44 (0) 8701 202530

1.4. Emergency telephone number

+44 1865 407333

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

No labelling applicable

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ALUMINIUM OXIDE	(CAS-No.) 90669-62-8 (EC-No.) 618-619-5	70	Not classified
SILICONE - A	(CAS-No.) 90337-93-2	27.5	
FIBREGLASS Continuous Filament	(CAS-No.) 65997-17-3	2.5	

Section 4: First aid measures

4.1. Description of first aid measures

- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact : Wash skin with plenty of water.
First-aid measures after eye contact : Rinse eyes with water as a precaution.
First-aid measures after ingestion : Call a poison centre or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/effects after inhalation : Inhalation may cause irritation (cough, short breathing, difficulty in breathing).
Symptoms/effects after skin contact : Causes mild skin irritation.
Symptoms/effects after eye contact : mild eye irritation.
Symptoms/effects after ingestion : Abdominal pain, nausea. May cause irritation to the digestive tract.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

Section 5: Fire fighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Water spray. Dry powder. Foam.

5.2. Special hazards arising from the substance or mixture

- Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

- Protection during fire fighting : Do not attempt to take action without suitable protective equipment.
Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

- Emergency procedures : Ventilate spillage area.

6.1.2. For emergency responders

- Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Mechanically recover the product.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

Section 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.

7.3. Specific end use(s)

No additional information available

Section 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Personal protective equipment:

Protective clothing. Safety glasses. Gloves.

Hand protection : Protective gloves

Eye protection : Safety glasses

Skin and body protection : Wear suitable protective clothing

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment

Personal protective equipment symbol(s):



Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Colour	: Grey.
Odour	: odourless.
Odour threshold	: No data available
pH	: Approx. 7
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: Not applicable
Boiling point	: > 35 °C
Flash point	: 321 °C
Auto-ignition temperature	: Not applicable
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 2.7
Solubility	: No data available

Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: Not applicable

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Section 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
	pH: Approx. 7
Serious eye damage/irritation	: Not classified
	pH: Approx. 7
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified

Fibreglass Continuous Filament (65997-17-3)

IARC group	3 - Not classifiable
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
 Acute aquatic toxicity : Not classified
 Chronic aquatic toxicity : Not classified

12.2. Persistence and degradability

Fibreglass Continuous Filament (65997-17-3)

Persistence and degradability : Not established.

12.3. Bioaccumulative potential

Fibreglass Continuous Filament (65997-17-3)

Bioaccumulative potential : No bioaccumulation data available.

12.4. Mobility in soil

No additional information available 12.5. Results of PBT and vPvB assessment
 No additional information available

12.6. Other adverse effects

No additional information available

Section 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport : Not regulated
 Transport by sea : Not regulated
 Air transport : Not regulated
 Inland waterway transport : Not regulated
 Rail transport : Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to REGULATION (EU) No 649/2012 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 4 July 2012 concerning the export and import of hazardous chemicals.

Substance(s) are not subject to Regulation (EC) No 850/2004 of the European Parliament and of the Council of 29 April 2004 on persistent organic pollutants and amending Directive 79/117/EEC.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

Section 16: Other information

No additional information available

Part Number
MPGCS-030-GF-150-0.5
MPGCS-030-GF-150-1.0
MPGCS-030-GF-150-1.5
MPGCS-030-GF-150-2.0
MPGCS-030-GF-150-3.0

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.