

Lenovo V14 ADA 82C6006CUK

Product

Lenovo V14 ADA

Region

WE

Country/Region

UK Group

Machine Type

82C6

TopSeller

TopSeller

Processor

AMD Ryzen 3 3250U (2C / 4T, 2.6 / 3.5GHz, 1MB L2 / 4MB L3)

Graphics

Integrated AMD Radeon Graphics

Chipset

AMD SoC Platform

Memory

4GB Soldered DDR4-2400 + 4GB SO-DIMM DDR4-2400

Storage

256GB SSD M.2 2242 PCIe 3.0x2 NVMe

Display

14" FHD (1920x1080) TN 220nits Anti-glare

Touchscreen

None

Optical

None

Card Reader

4-in-1 Card Reader

Ethernet

None

WLAN + Bluetooth

11ac, 2x2 + BT5.0

Camera

0.3MP

Microphone

Mono

Case Color

Iron Grey

Surface Treatment

Texture

Case Material

PC + ABS

Keyboard

Non-backlit, English (UK)

Fingerprint Reader

None

Security Chip

Firmware TPM 2.0

Battery

Integrated 35Wh

Power Adapter

65W Round Tip Wall-mount

Operating System

Windows 10 Home 64, English

Bundled Software

Office Trial

Base Warranty

1-year, Depot

Included Upgrade

None

EAN / UPC / JAN

195042436327

End of Support

2026-02-04

Announce Date

2020-02-13

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>


Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2021. All rights reserved.



Lenovo™

OVERVIEW



1. Power connector	5. Power indicator
2. HDMI 1.4b	6. NOVO button hole
3. USB 2.0	7. Headphone / microphone combo jack (3.5mm)
4. 2x USB 3.1 Gen 1	8. Card reader

PERFORMANCE

Processor

Processor Family

AMD 3000, AMD Athlon™ or AMD Ryzen™ 3 processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD 3020e	2	2	1.2GHz	2.6GHz	1MB L2 / 4MB L3	DDR4-2400	AMD Radeon™ Graphics
AMD Athlon Silver 3050U	2	2	2.3GHz	3.2GHz	1MB L2 / 4MB L3	DDR4-2400	AMD Radeon Graphics
AMD Athlon Gold 3150U	2	4	2.4GHz	3.3GHz	1MB L2 / 4MB L3	DDR4-2400	AMD Radeon Graphics
AMD Ryzen 3 3250U	2	4	2.6GHz	3.5GHz	1MB L2 / 4MB L3	DDR4-2400	AMD Radeon Graphics

Operating System

Operating System

- Windows® 10 Home 64
- Windows 10 Pro 64
- FreeDOS

Graphics

Graphics

Graphics	Type	Memory	Key Features
AMD Radeon Graphics	Integrated	Shared	DirectX® 12

Monitor Support

Monitor Support

Supports up to 2 independent displays via native display and 1 external monitor; supports external monitor via HDMI® (up to 3840x2160@30Hz)

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Memory Type

DDR4-2400

Memory Slots^[1]

- One memory soldered to systemboard, one DDR4 SO-DIMM slot
- One DDR4 SO-DIMM slot

Max Memory^[2]

- Up to 12GB (4GB soldered + 8GB SO-DIMM) DDR4-2400
- Up to 8GB (8GB SO-DIMM) DDR4-2400

Notes:

- A4-3020E model: One DDR4 SO-DIMM slot
- The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support

Up to two drives, 1x 2.5" HDD + 1x M.2 2242/2280 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 512GB

Storage Type

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-
M.2 2242 SSD	PCIe NVMe, PCIe 3.0 x2	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	-

Removable Storage

Optical

None

Card Reader

4-in-1 card reader (SD, SDHC, SDXC, MMC)

Multi-Media

Audio Chip

High Definition (HD) Audio

Speakers

Stereo speakers, 1.5W x2, Dolby® Audio™

Microphone

Single microphone

Camera

0.3-megapixel, fixed focus

Battery

Battery

- Integrated Li-Polymer 30Wh battery
- Integrated Li-Polymer 35Wh battery

Max Battery Life^[1]

- MobileMark® 2014: 5 hr (30Wh)
- MobileMark 2014: 6 hr (35Wh)

Notes:

1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, and/or JEITA 2.0 battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter

65W round tip (Wall Mount) AC adapter

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
14.0"	FHD (1920x1080)	None	TN	220 nits	Anti-glare	16:9	-	-	-	-
14.0"	HD (1366x768)	None	TN	220 nits	Anti-glare	16:9	-	-	-	-

14.0"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9	-	-	-	-
-------	--------------------	------	-----	----------	------------	------	---	---	---	---

Touchscreen

Non-touch

Notes:

1. California Electronic Waste Recycling Fee
- In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.
- For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, spill-resistant, multimedia Fn keys

Keyboard Backlight

Not support

Touchpad

Buttonless Mylar® surface multi-touch touchpad

Mechanical

Dimensions (WxDxH)

327.1 x 241 x 19.9 mm (12.88 x 9.49 x 0.78 inches)

Weight

1.6 kg (3.53 lbs)

Case Color

Iron grey

Surface Treatment

- IMR
- Texture

Case Material

PC + ABS (top), PC + ABS (bottom)

CONNECTIVITY

Network

Onboard Ethernet

No Ethernet

WLAN + Bluetooth™

802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 Card

Ports^[1]

Standard Ports^[2]

- 2x USB 3.1 Gen 1
- 1x USB 2.0
- 1x HDMI 1.4b
- 1x card reader
- 1x headphone / microphone combo jack (3.5mm)
- 1x power connector

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
- USB 2.0: 480 Mbit/s;
- USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
- USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
- USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
- Thunderbolt™ 3: 40 Gbit/s;

FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s

2. Depending on many factors, actual data transfer speed may be lower than theoretical speed

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Fingerprint Reader

No fingerprint reader

BIOS Security

- Power-on password
- Supervisor password
- Hard disk password

SERVICE

Warranty

Base Warranty

- 1-year depot service
- 2-year (1-yr battery) depot service

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F)

CERTIFICATIONS

Green Certifications

Green Certifications

- ErP Lot 3
- RoHS compliant



Lenovo V14 ADA

Lenovo™

