

Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LÖTLACK SK10
Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe BV
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Flammable liquid, category 2
Highly flammable liquid and vapour.



Productname : LÖTLACK SK10	Creationdate : 14.10.20	Version : 3.1
Ref.Nr.: BDS000463_3_20201014 (EN)	Replaces:	BDS000463_20170629

Classification is based on test data.

Health: Skin irritation, category 2
 Causes skin irritation.
 Eye irritation, category 2
 Causes serious eye irritation.
 Skin sensitization, category 1
 May cause an allergic skin reaction.
 Specific target organ toxicity - single exposure, category 3
 May cause drowsiness or dizziness.
 Aspiration Hazard Category 1
 May be fatal if swallowed and enters airways.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 3
 Harmful to aquatic life with long lasting effects.

Classification based on calculation method.

Other hazards : Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
 Rosin, colophony
 propan-2-ol; isopropyl alcohol; isopropanol
 acetone; propan-2-one; propanone
 1-methoxy-2-propanol; monopropylene glycol methyl ether

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H225 : Highly flammable liquid and vapour.
 H315 : Causes skin irritation.
 H319 : Causes serious eye irritation.
 H317 : May cause an allergic skin reaction.
 H336 : May cause drowsiness or dizziness.
 H304 : May be fatal if swallowed and enters airways.
 H412 : Harmful to aquatic life with long lasting effects.

Precautionary statement(s): P101 : If medical advice is needed, have product container or label at hand.
 P102 : Keep out of reach of children.
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P273 : Avoid release to the environment.
 P280 : Wear protective gloves/protective clothing/eye protection/face protection.
 P301/310 : IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.
 P333/313 : If skin irritation or rash occurs: Get medical advice/attention.
 P405 : Store locked up.
 P501-2 : Dispose of contents/container to an authorised waste collection point.

Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol; isopropanol	01-2119457558-25	67-63-0	200-661-7	25-50	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
acetone; propan-2-one; propanone	01-2119471330-49	67-64-1	200-662-2	25-50	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	A
1-methoxy-2-propanol; monopropylene glycol methyl ether	01-2119457435-35	107-98-2	203-539-1	10-25	Flam. Liq. 3, STOT SE 3	H226,H336	A
Rosin, colophony	01-2119480418-32	8050-09-7	232-475-7	5-10	Skin Sens. 1	H317	
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	01-2119475514-35	-	(921-024-6)1	5-10	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	B,Q

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention.
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur

Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

Ingestion : If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation : Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness

Ingestion : After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Symptoms : sore throat, abdominal pain, nausea, vomiting

Skin contact : Irritating to skin
May cause sensitization by skin contact.
Symptoms : redness and pain

Eye contact : Irritating to eyes
Symptoms : redness and pain, impaired vision

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

May form explosive vapour/air mixtures
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions



Productname : LÖTLACK SK10 Creationdate : 14.10.20 Version : 3.1
 Ref.Nr.: BDS000463_3_20201014 (EN) Replaces: BDS000463_20170629

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed, in a cool, well ventilated place.
 Keep out of reach of children.

7.3. Specific end use(s)

Anti Corrosion Products

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm



Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

		STEL	150 ppm
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
National established exposure limits, United Kingdom			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	1500 ppm
Rosin, colophony	8050-09-7	TWA	0.05 mg/m ³
		STEL	0.15 mg/m ³
National established exposure limits, Ireland			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	TWA	200 ppm
		STEL	400 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	-

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. It is good practice to wear gloves and to provide adequate ventilation whenever using the product. In all cases handle and use the product in accordance with good industrial hygiene practices.
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type AX)
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

6 / 11

Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

Appearance : physical state : Liquid.
colour : Yellow.
odour : Solvent.
pH : Not applicable.
Boiling point/range : Not available.
Flash point : - 35 °C (Closed Cup)
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 0.82 g/cm³ (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : > 200 °C
Viscosity : Not available.
< 7 mPa.s (@ 40°C).

9.2. Other information

VOC = volatile organic compounds 656 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO₂



Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	Causes skin irritation.
serious eye damage/irritation:	Causes serious eye irritation.
respiratory or skin sensitisation:	May cause an allergic skin reaction.
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	May be fatal if swallowed and enters airways.

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin May cause sensitization by skin contact.
Eye contact :	Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg
		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	LD50 oral rat	5840 mg/kg
		LC50 inhal.rat	> 25000 mg/l
		LD50 derm.rabit	13900 mg/kg
acetone; propan-2-one; propanone	67-64-1	LD50 oral rat	> 5800 mg/kg
		LC50 inhal.rat	76 mg/l
		LD50 derm.rabit	> 15800 mg/kg
Rosin, colophony	8050-09-7	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 25000 mg/m3
		LD50 derm.rat	> 2000 mg/kg

SECTION 12: Ecological information



Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3
Harmful to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
propan-2-ol; isopropyl alcohol; isopropanol	67-63-0	IC50 algae	1000 mg/l
		LC50 fish	9640 mg/l
		EC50 daphnia	9714 mg/l
acetone; propan-2-one; propanone	67-64-1	IC50 algae	530 mg/l
		LC50 fish	5540 mg/l
		EC50 daphnia	8800 mg/l
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	-	LC50 fish	> 10 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Do not discharge into drains or the environment, dispose to an authorised



Productname : LÖTLACK SK10 Creationdate : 14.10.20 Version : 3.1
Ref.Nr.: BDS000463_3_20201014 (EN) Replaces: BDS000463_20170629

waste collection point.

SECTION 14: Transport information

14.1. UN number

UN-number : 1263

14.2. UN proper shipping name

Proper shipping name: PAINT

14.3. Transport hazard class(es)

Class: 3
ADR/RID - Classification code: F1

14.4. Packing group

Packing group: II

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D/E)
IMDG - Ems: F-E, S-E
IATA/ICAO - PAX: 353
IATA/ICAO - CAO: 364

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)



Productname : LÖTLACK SK10
Ref.Nr.: BDS000463_3_20201014 (EN)

Creationdate : 14.10.20 Version : 3.1
Replaces: BDS000463_20170629

Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H317 : May cause an allergic skin reaction.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistent bioaccumulative toxic
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.