

(SKC0410-P01,02,140701)

Specifications			Ver.2.3	
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430511⊡K	Page: 2

4.Characteristics

4-1 Detection Performance (Detection Area A) Conditions for measuring: Ambient temperature=25°C(77°F) Operating voltage=3VDC

	Temperature difference	Value	Conditions concerning the target
(Note1)			1.Movement speed: 1.0m/s
Detection	2°C(3.6°F)	up to 5m	2.Target concept is human body
Range			(Object size:Around 700 × 250mm)

Note1:Depending on the temperature difference between the target and the surroundings, detection range will change.

		Value	Notes
	Horizontal	122°(±61°)	
Detection Area	Vertical	35° $\begin{pmatrix} +10^{\circ}\\ -25^{\circ} \end{pmatrix}$	Refer to the section 4-6.
	Detection zones	88	

4-2 Detection Performance (Detection Area B) Conditions for measuring: Ambient temperature=25°C(77°F) Operating voltage=3VDC

	Temperature difference	Value	Conditions concerning the target
^(Note1) Detection Range	4°C(7.2°F)	up to 5m	1.Movement speed: 1.0m/s 2.Target concept is human body (Object size:Around 700 × 250mm)

Note1:Depending on the temperature difference between the target and the surroundings, detection range will change.

		Value	Notes
	Horizontal	150°(±75°)	
Detection Area	Vertical	36°(±18°)	Refer to the section 4-6. (Ditection Area A is not included.)
	Detection zones	16	

Panasonic Corporation

Specifications				Ver.2.3
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430511⊡K	Page: 3

4-3 Maximum Rated Values


	Value	Unit
Power Supply Voltage	-0.3~4.5	VDC
Usable Ambient Temperature	-20 \sim +60°C (-4 \sim +140°F) Do not use in a freezing or condensation environment	
Storage Temperature	-20∼+70°C (-4∼+158°F)	


4-4 Electrical Characteristics

Conditions for Measuring: Ambient temperature=25°C(77°F)

	Symbol	Min	Avg.	Max	Unit	Special mention
Operating Voltage	Vdd	2.3	_	4.0	VDC	—
Electrical Current Consumption	Iw	—	6	12	μA	lout=0
Output Current	lout	—	_	100	μA	Vout≧Vdd−0.5
Output Voltage	Vout	Vdd-0.5	_	_	VDC	—
Circuit Stability Time (when voltage is applied)	Twu	_	_	10	S	This is when temperature of the sensor is stable

Issued on Nov. 1st,2020





Specifications				Ver.2.3
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430511∐K	Page: 6

5. Safety Precautions

Head the following precautions to prevent injury or accidents.

- Do not use these sensors under any circumstance in which the range of their ratings, environment conditions or other specifications are exceeded. Using the sensors in any way which causes their specifications to be exceeded may generate abnormally high levels of heat, emit smoke, etc., resulting in damage to the circuitry and possibly causing an accident.
- 2) Our company is committed to making products of the highest quality and reliability. Nevertheless, all electrical components are subject to natural deterioration, and durability of a product will depend on the operating environment and conditions of use. Continued use after such deterioration could lead to overheating, smoke or fire. Always use the product in conjunction with proper fire-prevention, safety and maintenance measures to avoid accidents, reduction in product life expectancy or break-down.
- Before connecting, check the pin layout by referring to the connector wiring diagram, specifications diagram, etc., to verify that the connector is connected properly. Mistakes made in connection may cause unforeseen problems in operation, generate abnormally high levels of heat, emit smoke, etc., resulting in damage to the circuitry.
- 4) Do not use any motion sensor which has been disassembled or remodeled.
- 5) Failure modes of sensors include short-circuiting, open-circuiting and temperature rises. If this sensor is to be used in equipment where safety is a prime consideration, examine the possible effects of these failures on the equipment concerned, and ensure safety by providing protection circuits or protection devices. Example :
 - ·Safety equipments and devices
 - Traffic signals
 - ·Burglar and disaster prevention

Panasonic Corporation


(SKC0410-P01,02,140701)

	Specifica	tions		Ver.2.3
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430511 K	Page: 7
6.Operating	Precautions			
6-1 Basic F	Principles			
However, heat sour	a pyroelectric infrared sensor th it may not detect in the following ce. Besides, it could also detect t and reliability of the system may	cases: lack c he presence (of movement, no temperatur of heat sources other than a	i human body.
1) Detect	ing heat sources other than the h	uman body, s	such as:	
b) When beam c) Sudd	l animals entering the detection a n a heat source for example sun l hit the sensor regardless inside o en temperature change inside or HVAC, or vapor from the humidifi	light, incande: or outside the around the d	detection area.	
2) Difficul	ty in sensing the heat source			
a cor b) Non-	s, acrylic or similar materials stan rect transmission of infrared rays movement or quick movements c se refer to 4-1 for details about m	, of the heat sou	urce inside the detection are	-
3) Expans	sion of the detection area			
	of considerable difference in the n area may be wider apart from t			y temperature,
4) Malfun	ction / Detection error			
output o	ssary detection signal might be o lue to the nature of pyro-electric on n strictly, please implement the c	element. Whe	en the application does not a	ccept such
6-2 Optima	I Operating Environment Condition	ons		
2) Humid 3) Pressu 4) Overhe 5) This se	erature : Please refer to the ma ity Degree :15~85% Rh (Avoid ire : 86~106kPa eating, oscillations, shocks can ca ensor is not waterproof or dustpro re, condensation, frost, containing	condensation ause the sens oof. Avoid use	n or freezing of this product) for to malfunction. in environments subject to	
	use in environments with corrosiv	-		

Issued on Nov. 1st,2020

Panasonic Corporation

		Specifica	ations		Ver.2.3
Product Name	PIR MOTION SEN	SOR "PaPIRs"	Model No.	EKMB430511⊡K	Page: 8
6-3 Handl	ing Cautions				
	ot solder with a sol sensor should be h	-	ove 350°C (662	$2^{\circ}F$), or for more than 3 sec	conds.
2) To m	aintain stability of t	he product, alv	vays mount or	n a printed circuit board.	
	ot use liquids to wa rmance.	sh the sensor.	If washing flu	id gets through the lens, it	can reduce
4) Do n	ot use a sensor afte	er it fell on the	ground.		
,	sensor may be dan ins and be very ca			c electricity. Avoid direct ha duct.	and contact with
,	n wiring the produc disturbances.	t, always use s	hielded cable	s and minimize the wiring I	ength to prevent
is hi	ghly recommendec je resistance : be	l.		age surge. Use of surge ab e value indicated in the ma	
Noise	e resistance : ±	10V or less (So	luare waves w	noise can cause operating vith a width of 50ns or 1µs) capacitor on the sensor's p	
<i>,</i> .	ating errors can be , broadcasting offic		se from static	electricity, lightning, cell pl	hone, amateur
10) Dete	ction performance	can be reduce	d by dirt on th	e lens, please be careful.	
,		•	• • •	lease avoid adding weight r reduced performance.	or impacts that
not g hum	guarantee durability idity levels will acc planned usage and	v or environme elerate the dete	ntal resistance erioration of el	uggested to prolong usage e. Generally, high temperat ectrical components. Pleas le expected reliability and le	tures or high se consider both
	ot attempt to clean ese can cause sha			ent or solvent, such as ber	nzene or alcohol,
envir	onments containing	g corrosive gas	s, dust, salty a	ronments. As well, avoid s ir etc. It could cause perfor llic connectors could be da	mance
T F	age conditions emperature: lumidity:	+5 ~ +40°C (- 30 ~ 75%)	
Plea	se use within 1 yea	ar after product	s delivery.		
leaved an Me	v. 1 st ,2020	D	20200	nic Corporati	ion



(SKC0410-P01,02,140701)

	Specifica	tions		Ver.2.3
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430511⊡K	Page: 10
7-3 Rec	ommended PCB Pattern Diagram +0.1 <u>3-∅0.65 0</u> (3-0.026 dia.) <u>∅5.08 ±0.1</u> (0.2 dia.)			
8.Special				
to change Please str	rements are continually being mad without notice. rictly follow the "Safety Precautions nctioning cannot be expected if us above.	s" and "Opera	ting Precautions" on the sp	pecifications she

We are deeply committed to providing the highest quality control for this product. Nevertheless:

- For issues not addressed above, we invite you to share your suggestions, or details about your company's usage conditions, installation, specifications, needs of end users, and applications for this sensor.
- 2) To reduce the risk of harm caused by product failure to human life or assets, this product should always be used in conjunction with other safety measures, such as protective circuitry, double layered circuit boards, etc., and used within the guaranteed performance, efficiency or special characteristics values stated in the specification sheet.
- 3) This product is warranted for a period of one year, from date of delivery, applicable only if the product is used in accordance with the precautions mentioned above and the specifications sheet. We will replace or repair at the delivery location any malfunctioning or defective part or entire product if such defect or malfunction is caused by us.

However, the above warranty shall be void in the following circumstances:

- a) Damage caused to something else than the product itself.
- b) Damage or loss resulting during transportation, storage or handling after the date of supply.
- c) Phenomenon unforeseeable in the state of the technology as of the supply date.
- d) Damage caused by natural or unnatural events such as fire, earthquake, flood, or conflicts beyond our control.

Issued on Nov. 1st,2020

Panasonic Corporation