

SPE PCB connector - SPE-T1-STSM-180 - 1163798

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




SPE PCB connector, type: IEC 63171-2, degree of protection: IP20, number of positions: 2, CAT B (ISO/IEC 63171), connection method: THR solder connection, Single Pair Ethernet

Your advantages

- ✓ Compact design for maximum space savings
- ✓ Connectors in accordance with IEC 63171-2
- ✓ Robust industrial design
- ✓ 360° shielding
- ✓ THR solderable
- ✓ Data transmission up to 600 MHz



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 063151 174095 |
| GTIN | 4063151174095 |
| Weight per Piece (excluding packing) | 4.020 g |

Technical data

Mechanical characteristics

| | |
|-----------------------------|-----------------------|
| Connection method | THR solder connection |
| Number of slots | 1 |
| Rated voltage (III/2) | 72 V DC |
| Insertion/withdrawal cycles | 750 |
| Number of positions | 2 |
| Degree of protection | IP20 |
| Degree of pollution | 2 |
| Locking type | Locking clip |

SPE PCB connector - SPE-T1-STSM-180 - 1163798

Technical data

Mechanical characteristics

| | |
|--|-------------|
| Weight | 4.02 g |
| Type | IEC 63171-2 |
| Flammability rating according to UL 94 | V0 |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Degree of protection | IP20 |

Material data

| | |
|--------------------------|--------------|
| Contact surface material | Ni/Au |
| Contact material | Copper alloy |
| Contact carrier material | LCP |
| Width | 5 mm |
| Height | 11.4 mm |
| Length | 9.3 mm |
| Mounting type | PCB mounting |

Electrical characteristics

| | |
|-----------------------------|-----------------------|
| Number of positions | 2 |
| GRP transmission properties | CAT B (ISO/IEC 63171) |
| Rated current | 4 A |
| Degree of pollution | 2 |
| Insulation resistance | > 1 TΩ |
| Test voltage Core/Core | 1000 V DC |
| Test voltage Core/Shield | 2250 V DC |

Standards and Regulations

| | |
|--|----------|
| Flame resistance | UL 94 V0 |
| Resistance to oil | yes |
| Halogen-free | yes |
| Flammability rating according to UL 94 | V0 |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27440390 |
| eCl@ss 11.0 | 27440390 |
| eCl@ss 9.0 | 27440402 |

Accessories

Accessories

Data cable preassembled

SPE PCB connector - SPE-T1-STSM-180 - 1163798

Accessories

Patch cable - SPE-T1-CCP-SF/1,0/AWG22/CCP-SF - 1183807



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 1 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

Patch cable - SPE-T1-CCP-SF/2,0/AWG22/CCP-SF - 1183808



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 2 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

Patch cable - SPE-T1-CCP-SF/3,0/AWG22/CCP-SF - 1183810



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 3 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

Patch cable - SPE-T1-CCP-SF/5,0/AWG22/CCP-SF - 1183811



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 5 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet
