

Patch cable - SPE-T1-CCP-SF/2,0/AWG22/CCP-SF - 1183808

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 2 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

Your advantages

- ✓ Compact design
- ✓ Connectors in accordance with IEC 63171-2
- ✓ Mechanical interlock with locking clip
- ✓ Robust industrial design
- ✓ 360° shielding
- ✓ Data transmission up to 600 MHz



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 222352
GTIN	4063151222352
Custom tariff number	85444290
Country of origin	Germany

Technical data

Dimensions

Length of cable	2.00 m
Width	7.53 mm
Height	14 mm

Ambient conditions

Patch cable - SPE-T1-CCP-SF/2,0/AWG22/CCP-SF - 1183808

Technical data

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

General data

Number of positions	2
Overvoltage category	I
Degree of pollution	2
Locking type	Locking clip
Rated voltage (III/2)	72 V DC
Connection method	Crimp connection
Insertion/withdrawal cycles	≥ 750
Contact material	Cu alloy
Contact carrier material	LCP
Contact surface material	Au
Number of slots	2
Rated current	4 A
Number of positions	2
Connection cross section AWG	22 ... 22
Transmission speed	1 Gbps ()
	100 Mbps ()
	10 Mbps ()

Standards and Regulations

Flame resistance	UL 94 V0
Resistance to oil	yes
Halogen-free	yes
Other resistance	UV resistant
Flammability rating according to UL 94	V0
Standards/regulations	IEC 63171
	IEC 63171-2
	IEEE 802.3bu
	IEEE 802.3cg
	IEEE 802.3bw
	IEEE 802.3bp

Patch cable - SPE-T1-CCP-SF/2,0/AWG22/CCP-SF - 1183808

Classifications

eCl@ss

eCl@ss 10.0.1	27440390
eCl@ss 11.0	27440392
eCl@ss 9.0	27440390

Accessories

Accessories

Female insert

SPE PCB connector - SPE-T1-STRM-90 - 1163797



SPE PCB connector, type: IEC 63171-2, degree of protection: IP20, number of positions: 2, CAT B (ISO/IEC 63171), connection method: THR solder connection, Single Pair Ethernet

SPE PCB connector - SPE-T1-STSM-180 - 1163798



SPE PCB connector, type: IEC 63171-2, degree of protection: IP20, number of positions: 2, CAT B (ISO/IEC 63171), connection method: THR solder connection, Single Pair Ethernet