

Product Data Sheet



FP701-3ED

artnr. 938140

Safety Products



- Description:** Two colour type harness with sliding anchorage dorsal point with webbing extension and 2 chestloops.
- Materials:** 44mm Polyamide webbing
Colour: Orange shoulderstraps / Green legstraps.
Zinc plated-steel adjustment buckles.
- Weight:** 0,975 kg
- Standards:** EN361 / ANSI Z359.1 / CSA Z259.10
- Performance** Single size : Medium up to large.
Length adjustable legstraps with quick buckles.
Delivery without karabiner
- Packaging:** polyethene bag

EN 361 - A body support for fall arrest purposes. The full body harness suitably arranged and assembled to support the whole body of a person and to restrain the wearer during and after the fall.

EN 361	Standard characteristics
<p>Full Body Harness</p>	<p>Characteristics</p> <p>Static tests</p>
Traction upwards 15 kN / (3min)	Test 1 Force and time of application
Traction downwards 10 kN / (3min)	Test 2 Force and time of application
4m	Dynamic tests Free fall
100 kg / 2m 1 Head up	Dummy and lanyard length Number and fall type
1 Head down	