

2363638-1 ✓ ACTIVE

TE Internal #: 2363638-1

Zhaga Book 18 Street Lighting Connectors, Connector, Black
Housing Color, Product Height 27.4 mm, Keyed / Not Vented,
Zhaga, 4 Position, Sealable

[View on TE.com >](#)



Connectors > Lighting Connectors > Street Lighting Controls > Zhaga Book 18 Street Lighting Connectors



Lighting Product Type: **Connector**

Housing Color: **Black**

Product Height: **27.4 mm**

Lighting Connector Features Included: **Keyed, Not Vented**

Agency/Standard: **Zhaga**

Features

Product Type Features

Lighting Product Type	Connector
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Lighting Connector Features Included	Keyed, Not Vented
Number of Positions	4

Contact Features

Contact Current Rating (Max)	1.5 A
------------------------------	-------

Housing Features

Housing Color	Black
---------------	-------

Dimensions

Product Diameter	36.5 mm
Product Height	27.4 mm

Usage Conditions



IP Water Sealing Level	6
IP Dust Sealing Level	6
Operating Temperature Range	-40 – 90 °C[-40 – 190 °F]

Industry Standards

Agency/Standard	Zhaga
-----------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

[Recept, LUMAWISE Endurance S2 Kit, Zhaga](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2363638-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2363638-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2363638-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Lumawise Endurance S Modules

English

Product Specifications

Application Specification

English