



SAFETY DATA SHEET PREMIUM RED ANTIFREEZE

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name PREMIUM RED ANTIFREEZE
Product number FSA001, FSA002, FSA005, FSA025, FSA199

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Antifreeze liquid.

1.3. Details of the supplier of the safety data sheet

Supplier TETROSYL FRANCE
 ZAC du Moulin
 40, avenue Clément Ader
 59118 WAMBRECHIES
 TEL: 03 20 28 06 30
 qualite@tetrosyl-france.com

Manufacturer TETROSYL LIMITED
 Bury
 Lancashire
 England
 BL9 7NY
 0161 764 5981
 0161 797 5899
 info@tetrosyl.com

1.4. Emergency telephone number

Emergency telephone +44 (0)161 764 5981

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified
Health hazards Acute Tox. 4 - H302 Eye Irrit. 2 - H319 STOT RE 2 - H373
Environmental hazards Not Classified

Human health See Section 11 for additional information on health hazards.

2.2. Label elements

Hazard pictograms



Signal word Warning

PREMIUM RED ANTIFREEZE

Hazard statements	H302 Harmful if swallowed. H319 Causes serious eye irritation. H373 May cause damage to organs through prolonged or repeated exposure.
Precautionary statements	P260 Do not breathe vapour/ spray. P264 Wash contaminated skin thoroughly after handling. P270 Do not eat, drink or smoke when using this product. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P314 Get medical advice/ attention if you feel unwell. P330 Rinse mouth. P337+P313 If eye irritation persists: Get medical advice/ attention. P501 Dispose of contents/ container in accordance with national regulations. P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children.
Contains	ETHANEDIOL

2.3. Other hazards

This product contains substances classified as PBT.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

ETHANEDIOL	60-100%
CAS number: 107-21-1	EC number: 203-473-3
	REACH registration number: 01-2119456816-28-0000
Classification	
Acute Tox. 4 - H302	
STOT RE 2 - H373	
POTASSIUM 2-ETHYL HEXANOATE	2-<3%
CAS number: 3164-85-0	EC number: 221-625-7
Classification	
Skin Irrit. 2 - H315	
Eye Dam. 1 - H318	
Repr. 2 - H361d	

The full text for all hazard statements is displayed in Section 16.

Composition comments The data shown are in accordance with the latest EC Directives.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information Effects may be delayed. Keep affected person under observation. For breathing difficulties, oxygen may be necessary. If breathing stops, provide artificial respiration. Get medical attention. Remove affected person from source of contamination. Place unconscious person on the side in the recovery position and ensure breathing can take place. Never give anything by mouth to an unconscious person.

PREMIUM RED ANTIFREEZE

Inhalation	Remove affected person from source of contamination. Get medical attention if any discomfort continues. For breathing difficulties, oxygen may be necessary. If breathing stops, provide artificial respiration. If spray/mist has been inhaled, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. If throat irritation or coughing persists, proceed as follows. Get medical attention. Show this Safety Data Sheet to the medical personnel.
Ingestion	Get medical attention immediately. Never give anything by mouth to an unconscious person. Try to induce vomiting. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Rinse mouth thoroughly with water. Give plenty of water to drink. Get medical attention if a large quantity has been ingested. Show this Safety Data Sheet to the medical personnel.
Skin contact	Remove contaminated clothing and rinse skin thoroughly with water. Get medical attention if any discomfort continues.
Eye contact	Do not rub eye. Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention if irritation persists after washing. Show this Safety Data Sheet to the medical personnel.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.
Inhalation	Irritation of nose, throat and airway.
Ingestion	May cause discomfort if swallowed. May cause unconsciousness, blindness and possibly death. Central nervous system depression.
Skin contact	Prolonged skin contact may cause redness and irritation.
Eye contact	Irritation, burning, lachrymation, blurred vision after liquid splash.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations. If in doubt, get medical attention promptly.
-----------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	No unusual fire or explosion hazards noted.
Hazardous combustion products	Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	No specific firefighting precautions known.
Special protective equipment for firefighters	Leave danger zone immediately.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

PREMIUM RED ANTIFREEZE

Personal precautions For personal protection, see Section 8. In case of spills, beware of slippery floors and surfaces.

6.2. Environmental precautions

Environmental precautions Collect and dispose of spillage as indicated in Section 13.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up For waste disposal, see Section 13. Wear protective clothing as described in Section 8 of this safety data sheet. Provide adequate ventilation. Contain spillage with sand, earth or other suitable non-combustible material. Avoid the spillage or runoff entering drains, sewers or watercourses. Absorb spillage with non-combustible, absorbent material. Contact Health and Safety department on 6695 for further assistance.

6.4. Reference to other sections

Reference to other sections Wear protective clothing as described in Section 8 of this safety data sheet. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Read and follow manufacturer's recommendations. Keep away from heat, sparks and open flame. Wear suitable protective equipment for prolonged exposure and/or high concentrations of vapours, spray or mist. Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Avoid inhalation of vapours/spray and contact with skin and eyes. Avoid the formation of mists. Observe any occupational exposure limits for the product or ingredients. Avoid inhalation of vapours and spray/mists. Pregnant or breastfeeding women should not work with this product if there is any risk of exposure. Pregnant or breastfeeding women should not work with this product if there is any risk of exposure.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Keep away from heat, sparks and open flame. Keep container tightly closed. Keep containers upright. Keep only in the original container. Avoid contact with oxidising agents.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

No exposure limits known for ingredient(s).

ETHANEDIOL

Long-term exposure limit (8-hour TWA): WEL 20 ppm 52 mg/m³ vapour

Short-term exposure limit (15-minute): WEL 40 ppm 104 mg/m³ vapour

Sk

Long-term exposure limit (8-hour TWA): WEL 10 mg/m³ particulate

Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through the skin.

8.2. Exposure controls

PREMIUM RED ANTIFREEZE

Protective equipment



Appropriate engineering controls

Avoid inhalation of vapours. Observe any occupational exposure limits for the product or ingredients. Provide adequate ventilation.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

It is recommended that gloves are made of the following material: Nitrile rubber. Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible.

Other skin and body protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

Provide eyewash station. Wash contaminated clothing before reuse. Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

Respiratory protection

No specific recommendations. Respiratory protection must be used if the airborne contamination exceeds the recommended occupational exposure limit.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid. Hygroscopic. Viscous liquid.
Colour	Red. Orange.
Odour	Odourless. or No characteristic odour.
pH	pH (concentrated solution): 7.5 - 8.5
Melting point	-12°C
Initial boiling point and range	197°C @ 760 mm Hg
Flash point	111°C Closed cup.
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	0.05 kPa @ °C
Vapour density	Not determined.
Relative density	1.10 @ 20°C
Solubility(ies)	Miscible with water. Miscible with the following materials: acetone Alcohols.
Partition coefficient	: -1.36
Auto-ignition temperature	400°C
Decomposition Temperature	Not determined.

9.2. Other information

PREMIUM RED ANTIFREEZE

Other information None.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity The following materials may react with the product: Oxidising materials.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions Not determined.

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition.

10.5. Incompatible materials

Materials to avoid Strong acids. Strong oxidising agents. Strong alkalis.

10.6. Hazardous decomposition products

Hazardous decomposition products Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects No information available.

Acute toxicity - oral

ATE oral (mg/kg) 526.32

Specific target organ toxicity - single exposure

Target organs Central nervous system Heart and cardiovascular system Kidneys

Inhalation Unlikely to be hazardous by inhalation because of the low vapour pressure of the product at ambient temperature. Vapours may irritate throat/respiratory system. Symptoms following overexposure may include the following: Coughing.

Ingestion Harmful if swallowed.

Skin contact Prolonged and frequent contact may cause redness and irritation.

Eye contact Causes serious eye irritation.

Acute and chronic health hazards May cause liver and/or renal damage. Possible risk of adverse reproductive effects. A single exposure may cause the following adverse effects: Central nervous system depression. May cause damage to the kidneys. May cause damage to the kidneys. Contains a substance/a group of substances which may damage fertility and the unborn child.

Route of exposure Ingestion.

Target organs Central nervous system Heart & cardiovascular system Kidneys

Medical symptoms Allergic rash. Delayed, often serious, breathing problems. Tachycardia (excessively rapid heart beat, including rapid and weak pulse). Unconsciousness, possibly death.

SECTION 12: Ecological information

PREMIUM RED ANTIFREEZE

Ecotoxicity The product components are not classified as environmentally hazardous. However, large or frequent spills may have hazardous effects on the environment.

12.1. Toxicity

Acute aquatic toxicity

Acute toxicity - fish LC₅₀, 96 hours: 72860mg/l mg/l, Fish

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: >100mg/l mg/l, Daphnia magna

Acute toxicity - aquatic plants IC₅₀, 72 hours: >6500mg/l mg/l, Algae

12.2. Persistence and degradability

Persistence and degradability The product is biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential The product is not bioaccumulating.

Partition coefficient : -1.36

12.4. Mobility in soil

Mobility The product is miscible with water and may spread in water systems.

Adsorption/desorption coefficient Not available.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current EU criteria.

12.6. Other adverse effects

Other adverse effects Not applicable.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Confirm disposal procedures with environmental engineer and local regulations.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

PREMIUM RED ANTIFREEZE

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78
and the IBC Code**

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations EH40/2005 Workplace exposure limits.

EU legislation Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments NOTE: Lines within the margin indicate significant changes from the previous revision.

Issued by Health & Safety Department

Revision date 04/02/2021

Revision 13

Supersedes date 29/01/2020

SDS status Approved.

Hazard statements in full H302 Harmful if swallowed.
H315 Causes skin irritation.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H361d Suspected of damaging the unborn child.
H373 May cause damage to organs (Kidneys) through prolonged or repeated exposure.
H373 May cause damage to organs through prolonged or repeated exposure.