# **DC Brushless Blower** 12V DC, 50mm x 50mm x 20mm Multicomp PRO



RoHS **Compliant** 



## **Mechanical Characteristic**

Motor Design : Brushless DC motor. Bearing System : Vapo Bearing System

Materials of Frame : Thermoplastic PBT of UL 94V-0 : Thermoplastic PBT of UL 94V-0 Materials of Fan Blade

Direction of Rotation : Counter-Clockwise Viewed From Front of Fan Blade

Mounting Holes : Diameter 4.5 mm In 2 Holes

Weight : 34g

#### **Electric Characteristic**

Rated Voltage : 12V DC

Rated Current : 124 mA / Max. 137 mA

Rated Power Consumption : 1.49 WATTS / Max. 1.65 WATTS

Safety Power Consumption : 1.68 WATTS

Operating Voltage Range : 4.5V DC to 13.8V DC

Starting Voltage : 4.5V DC (25°C Power ON/OFF)

Operating Temperature Range : -10°C to + 70°C Storage Temperature Range : -40°C to + 70°C

### **Performance Characteristic**

Rated Speed : 5300 RPM ± 15% at rated voltage

Air Flow : 5.8 CFM Static Pressure : 0.66 Inch-H<sub>2</sub>O Acoustic Noise : 34.8 dB(A) Insulation Class : UL Class A

Insulation Resistance Plastic Housing :  $10M\Omega$  at 500V DC between internal stator and Lead wire (+)

: Applied AC 500 V for one minute or AC 600 V for 2 Seconds between housing and Dielectric Strength

lead wire (+)

Life Expectancy : 60,000 hours at 40°C, 65% humidity, 90% CL.

Protection : Automatic Restart

Note: The motor will shut down when rotor was locked, then auto restart within

10 seconds.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




# **DC** Brushless Blower 12V DC, 50mm x 50mm x 20mm Multicomp PRO



## Safety

SAFETY	UL	CUR	TUV	CE
NO.	E77551	E77551	✓	✓


### Air Flow & Static Pressure Curve



# **DC Brushless Blower** 12V DC, 50mm x 50mm x 20mm Multicomp PRO



### **Dimensions**



Dimensions: Millimetres

## **Part Number Table**

Description	Part Number
DC Brushless Blower, Vapo Bearing, 12V DC, 50mm x 50mm x 20mm, 2 Wire Leads	MP007137

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

