



# PRODUCT SPECIFICATION

<b>Brand</b>	Kasp
<b>Product Range</b>	Shutter Lock
<b>Catalogue number</b>	170
<b>Date</b>	08/03/2007

**Range Description**  
Brass Shutter Locks

- Features**
- Hardened steel shackle – extra protection against hacksaw and cropping attacks
  - Solid brass body – added resistance to corrosion
  - 5 Pin cylinder with anti pick mushroom pins – extra protection against picking
  - Paracentric keyway extra protection against manipulation

These padlocks are supplied display packed in sealed blisters or individually boxed

2 keys are supplied with each lock



Item Number	Item Description	EAN No	Commodity code	Carton Qty
K17063D	Brass shutter lock 63mm – display packed	5013969901092	83011000	6
K17070D	Brass shutter lock 70mm – display packed	5013969901108	83011000	6
K17070	Brass shutter lock 70mm – boxed	5013969902549	83011000	6
K17090D	Brass shutter lock 90mm – display packed	5013969901115	83011000	6

<p>Technical product information</p>	<p><b>Body</b> – Solid brass</p> <p><b>Shackle</b>- Hardened alloy steel, chrome plated</p> <p><b>Locking mechanism</b>- Pin tumbler cylinder type, 5 pin cylinder, Brass pins – Top pin 5 is plain, top pins 1 to 4 are mushroom type.</p> <p><b>Key differs</b>- 1988</p> <p><b>Re-keyable</b> – No</p> <p><b>Security rating:</b></p> <table border="1" data-bbox="483 741 865 947"> <thead> <tr> <th>Item</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K17063D</td> <td>8</td> </tr> <tr> <td>K17070D</td> <td>9</td> </tr> <tr> <td>K17070</td> <td>9</td> </tr> <tr> <td>K17090D</td> <td>11</td> </tr> </tbody> </table> <p><b>Shackle Dimensions:</b></p> <table border="1" data-bbox="483 1055 1197 1312"> <thead> <tr> <th rowspan="2">Dimensions mm</th> <th colspan="3">Shackle</th> <th>Body</th> </tr> <tr> <th>Dia</th> <th>Internal width</th> <th>Internal height</th> <th>Width</th> </tr> </thead> <tbody> <tr> <td>K17063D</td> <td>10</td> <td>19</td> <td>14</td> <td>64</td> </tr> <tr> <td>K17070D</td> <td>12</td> <td>22</td> <td>13</td> <td>70</td> </tr> <tr> <td>K17070</td> <td>12</td> <td>22</td> <td>13</td> <td>70</td> </tr> <tr> <td>K17090D</td> <td>12</td> <td>35</td> <td>18</td> <td>90</td> </tr> </tbody> </table> <p><b>Use environment</b>- Normal outdoor use</p> <p><b>Recommended applications</b>- Specifically designed for shutters, grilles and use with chain, the shutter lock is increasingly used for a wide range of applications in industrial and commercial premises</p>	Item	Security rating	K17063D	8	K17070D	9	K17070	9	K17090D	11	Dimensions mm	Shackle			Body	Dia	Internal width	Internal height	Width	K17063D	10	19	14	64	K17070D	12	22	13	70	K17070	12	22	13	70	K17090D	12	35	18	90
Item	Security rating																																							
K17063D	8																																							
K17070D	9																																							
K17070	9																																							
K17090D	11																																							
Dimensions mm	Shackle			Body																																				
	Dia	Internal width	Internal height	Width																																				
K17063D	10	19	14	64																																				
K17070D	12	22	13	70																																				
K17070	12	22	13	70																																				
K17090D	12	35	18	90																																				
Standards compliance	None applicable																																							
User health and safety information	None applicable																																							
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations																																							
Material safety data	None applicable																																							
Warranty	KASP shutter locks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered																																							
Country of origin	China																																							

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K17063D	63	16	44	296	140	23	170	333
K17070D	71	18	50	426	140	23	170	463
K17070	71	18	50	426	73	19	52	434
K17090D	90	20	60	702	150	28	190	747

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K17063D	145	220	85	2085		
K17070D	145	220	85	2865		
K17070	72	140	95	2652		
K17090D	160	260	105	4597		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K17063D	31	Blister	6	Backing card			87	Box
K17070D	31	Blister	6	Backing card			87	Box
K17070			8	Box			48	Box
K17090D	37	Blister	8	Backing card			115	Box