



Main

Product or component type	Uninterruptible power supply (UPS)
Provided equipment	1 USB software CD 1 RS232 USB cable 1 user manual
Mounting support	Floor-standing
Communication port protocol	USB RS232
Function available	Intelligent charging algorithm monitors battery and AC supply Battery monitoring Audible alarm when a fault condition arises Internal bypass Optional communication kit for remote monitoring
Topology	Line interactive

Complementary

Display type	LCD display
Integrated connection type	USB port RS232
Type of signal	Sine wave
Protection device type	Surge protection device (SPD) Miniature circuit breaker (MCB)
Protection type	Surge arrester Fuse
Input voltage	230 V AC 220 V AC 240 V AC
Output voltage	230 V AC nominal mode 220 V AC 240 V AC
IP degree of protection	IP20
Transfer time	6 ms
Network frequency	44...66 Hz
Power range	750 VA
Electrical connection	Output: 6 outlet IEC 320 C13 Input: 1 inlet IEC 320 C14

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Local signalling	Alarm, distinctive for low battery LCD display, continuous or intermittent tone for overload LCD display for status and alert
Battery type	Lead-acid battery Sealed rechargeable
Number of batteries	2
Charging time	6 h
Battery voltage	12 V
Battery capacity	7 Ah
Battery life	5 year(s)
Quantity per set	Set of 1
Net weight	13.6 kg
Height	220 mm
Width	160 mm
Depth	410 mm

Environment

Relative humidity	0...95 %, non-condensing
Operating altitude	0...3000 m
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-10...40 °C
Product certifications	CE

Contractual warranty

Warranty	2 years
----------	---------