

Technical Data Sheet

PolyDissolve™ S2

www.polymaker.com

V5.0



PolyDissolve™ S2

PolyDissolve™ S2 is a dissolvable support for PC, ABS and ASA based filaments from our portfolio. It is specifically engineered to have a perfect interface with these materials while also displaying good solubility.


PHISICAL PROPERTIES

Property	Testing Method	Typical Value
Density	ISO1183, GB/T1033	1.37 g/cm ³ at 21°C
Melt Index	220°C, 2.16kg	7.8 g/10min

THERMAL PROPERTIES

Property	Testing Method	Typical Value
Glass transition	DSC, 10°C/min	61 °C
Vicat softening temperature	ISO 306 GB/T 1633	62.9 °C

MOISTURE ABSORPTION CURVE



Material Compatibility

Material	Adhesion with PolyDissolve™ S2
PLA based material from Polymaker's portfolio	N/A
PETG based material from Polymaker's portfolio	N/A
ABS based material from Polymaker's portfolio	++
PC based material from Polymaker's portfolio	++
PVB based material from Polymaker's portfolio	N/A
TPU based material from Polymaker's portfolio	N/A
Nylon based material from Polymaker's portfolio	+

++ support the model very well

+ generally support the model depending on its geometry

- generally doesn't support the model depending on its geometry

-- do not support the model

Warning: PolyDissolve S2 needs to be dissolved in 75°C lye, it isn't recommended to work with PVA and PLA based filaments

Note:

- PolyDissolve™ S2 can be used without moisture-proof treatment.

DISCLAIMER:

The typical values presented in this data sheet are intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. Actual values may vary significantly with printing conditions. End- use performance of printed parts depends not only on materials, but also on part design, environmental conditions, printing conditions, etc. Product specifications are subject to change without notice.

Each user is responsible for determining the safety, lawfulness, technical suitability, and disposal/ recycling practices of Polymaker materials for the intended application. Polymaker makes no warranty of any kind, unless announced separately, to the fitness for any use or application. Polymaker shall not be made liable for any damage, injury or loss induced from the use of Polymaker materials in any application.