

SB 18 LTX BL I (602352500) Cordless hammer drill
18V 2x4Ah Li-ion; Charger ASC 55 (220-240 V / 50 - 60 Hz); Plastic Carry Case

Order no. 602352500
EAN 4007430297945



Product may differ from Image



- Brushless hammer drill with maximum power for demanding applications
- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Unique Metabo brushless motor for quick work progress and highest efficiency when drilling and screwdriving
- Precision Stop: electronic torque control with increased precision for precise, delicate working
- High-performance impact mechanism for optimum drilling performance
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Collar (Ø 43 mm) for versatile use
- Integrated working light to illuminate the contact area
- Robust die cast aluminium gear housing for optimum heat dissipation and long service life
- With handy belt hook and bit case which can be fixed either on the right or left side

Technical data

Characteristics

Type of battery pack	Li-ion
Battery voltage	18 V
Battery pack capacity	2 x 4 Ah
Maximum torque - soft	60 Nm
Pulse torque	65 Nm
Maximum torque, hard	120 Nm
Adjustable torque	1 - 20 Nm
Drill-Ø masonry	16 mm
Drill Ø steel	13 mm
Drill-Ø soft wood	65 mm
No-load speed	0 - 500 / 0 - 1850 rpm
Maximum impact rate	32300 bpm
Chuck capacity	1.5 - 13 mm
Weight (including battery pack)	2.4 kg

Vibration

Drilling in metal	3.2 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Impact drilling concrete	20.7 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	92 dB(A)
Sound power level (LwA)	103 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

Futuro Plus keyless chuck with metal sleeve
 Side handle
 Belt hook and bit case
 2 Li-Power battery packs (18 V/4.0 Ah)
 Charger ASC 55 "AIR COOLED"
 Plastic carry case