



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2-2151517-1 OCEAN_2.0_Applicator-S-042F062O	 TE Part # 2-2151517-2 OCEAN_2.0_Applicator-S-042F062O	 TE Part # 2151517-1 OCEAN_2.0_Applicator-S-042F062O	 TE Part # 2151517-2 OCEAN_2.0_Applicator-S-042F062O
 KIT OCEAN_2.0_SPARE_PART_KIT-042F062O	 TE Part # 567373-2 HDM SMPR042F070F K 770601	 TE Part # 567373-3 APPL,HDM 5SMPR042F070F G	 TE Part # 567910-1 SCA 9SMPR042F070F S

Customers Also Bought

 TE Part #1-640457-3 Polyester Right Angle PCB Header: 2.54mm, Unshrouded, MTA 100	 TE Part #1375820-7 Receptacle Housing: 2.54mm, 1 Row, CST-100 II	 TE Part #207542-1 HSG,PLUG 16 POSN,METRIMATE	 TE Part #1338689-1 ANVIL, COMBINATION .042
 TE Part #2-683454-4 CRIMPER, INSUL "O" (.055")	 TE Part #2-2119582-0 Crimper, Insulation F Premium	 TE Part #121397P013 ES2000-NO.3-B8-0-41MM	 TE Part #CX1859-000 V2-1.0-0-23MM

Documents

- Datasheets & Catalog Pages
- CRIMPING WHERE FORM MEETS FUNCTION
- English
- Instruction Sheets
- Instruction Sheet (U.S.)



English