

*Safety data sheet*  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1 Product identifier**

· Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61  
Positive disposer, can 1 liter Ref: AR61

· 1.2 Relevant identified uses of the substance or mixture and uses advised against  
commercial and/or industrial use

· Application of the substance / the preparation : Reagent

**1.3 Details of the supplier of the safety data sheet**

· Manufacturer/Supplier:

CIF

240 rue Hélène Boucher

78530 BUC

Tél : 01.39.66.96.83 – Fax 01.33.66.97.78

E-mail : cif@cif.fr – Web : www.cif.fr

**1.4 Emergency telephone number:**

France (ORFILA 24h/24) - Tel : +33 (0)1 45 42 59 59

Ireland - Tel : 00 353 1 8092568 - 00 353 1 83 79964 (24h/24)

UK : +44 (0)-870-190-6777 (CARECHEM24)

**SECTION 2: Hazards identification****2.1 Classification of the substance or mixture**

· Classification according to Regulation (EC) No 1272/2008 :



GHS05

Met. Corr.1 H290 May be corrosive to metals.

Skin Corr. 1A H314 Causes severe skin burns and eye damage.

Eye Dam. 1 H318 Causes serious eye damage.

**2.2 Label elements**

· Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms



GHS05

· Signal word Danger

· Hazard-determining components of labelling:

sodium hydroxide

· Hazard statements

H290 May be corrosive to metals.

H314 Causes severe skin burns and eye damage.

· Precautionary statements

P260 Do not breathe dust/fume/gas/mist/vapours/spray.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P234 Keep only in original container.

P264 Wash hands thoroughly after handling.

(Contd. on page 2)



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

(Contd. of page 1)

P303 + P361 + P353 **IF ON SKIN ( or hair):** Take off immediately all contaminated clothing. Rinse skin with water/shower.

P305 + P351 + P338 **IF IN EYES:** Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P304 + P340 **IF INHALED:** Remove person to fresh air and keep comfortable for breathing.

P301 + P330 + P331 **IF SWALLOWED:** rinse mouth. Do NOT induce vomiting.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

- **3.2 Chemical characterisation: Mixtures**
- **Description:** Mixture: consisting of the following components.

- **Dangerous components:**

CAS: 1310-73-2 EINECS: 215-185-5 Index number: 011-002-00-6 Reg.nr.: 01-2119457892-27	sodium hydroxide	 Met. Corr.1, H290; Skin Corr. 1A, H314	50-100%
--	------------------	--	---------

- **Additional information:** For the wording of the listed risk phrases, refer to section 16.

### SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After excessive inhalation:**  
In case of unconsciousness place patient in a stable laying down side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed :**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed :**  
No further relevant information available.

### SECTION 5: Firefighting measures

- **5.1 Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture :**  
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters**
- **Protective equipment:** Wear self-contained respiratory protective device.

(Contd. on page 3)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

(Contd. of page 2)

### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures :**  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow the product to enter sewers/surface water or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Use neutralising agent.  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **6.4 Reference to other sections :**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protective equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling :**  
Open and handle receptacle with care.  
Prevent formation of dust.  
Keep receptacles tightly sealed.  
Thorough dedusting.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**  
· **Requirements to be met by storerooms and receptacles:** No special requirements.  
· **Information about storage in one common storage facility:**  
Store away from metals.  
Store away from foodstuffs.  
Do not store together with acids.  
Store away from water.
- **Further information about storage conditions:**  
Store receptacle in a well ventilated area.  
Protect from heat and direct sunlight.  
This product is hygroscopic.  
Protect from humidity and water.  
Keep container tightly sealed.
- **7.3 Specific end use(s) :** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see section 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

**1310-73-2 sodium hydroxide (50-100%)**

WEL ( Great Britain)	Short-term value: 2 mg/m <sup>3</sup>
MAK ( Switzerland)	Short-term value: 2 e mg/m <sup>3</sup>
	Long-term value: 2 e mg/m <sup>3</sup>
	SSc;

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

(Contd. of page 3)

· **Additional information:**

The most current valid lists have been used as a basis for the production of this document.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from food, beverages and pet food.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

· **Respiratory protection:** Not required.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

· **Gloves material:**

The selection of suitable gloves does not depend only on the material, but also on further marks of quality which may vary from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked before use.

· **Eye protection:**



Tightly sealed goggles

## SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Solid

Colour: White

· **Odour:** Odourless

· **Odour threshold:** Not determined.

· **pH-value (100 g/l) at 20 °C:** >14

· **Change in condition**

Melting point/Melting range: 319 °C

Boiling point/Boiling range: 1390 °C

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not determined.

· **Ignition temperature:** Not applicable.

· **Decomposition temperature:** Not determined.

· **Self-igniting:** Product is not self-igniting.

(Contd. on page 5)



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

(Contd. of page 4)

· <b>Danger of explosion:</b>	<i>Product does not present an explosion hazard.</i>
· <b>Explosion limits:</b>	
<b>Lower:</b>	<i>Not determined.</i>
<b>Upper:</b>	<i>Not determined.</i>
· <b>Vapour pressure:</b>	<i>Not applicable.</i>
· <b>Density at 20 °C:</b>	<i>2,13 g/cm<sup>3</sup></i>
· <b>Relative density:</b>	<i>Not determined.</i>
· <b>Vapour density:</b>	<i>Not applicable.</i>
· <b>Evaporation rate:</b>	<i>Not applicable.</i>
· <b>Solubility in / Miscibility with water at 20 °C:</b>	<i>1260 g/l</i>
· <b>Segregation coefficient (n-octanol/water):</b>	<i>Not determined.</i>
· <b>Viscosity:</b>	
<b>Dynamic:</b>	<i>Not applicable.</i>
<b>Kinematic:</b>	<i>Not applicable.</i>
· <b>9.2 Other information:</b>	<i>No further relevant information available.</i>

### **SECTION 10: Stability and reactivity**

- **10.1 Reactivity** *No further relevant information available.*
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** *No decomposition if used according to specifications.*
- **10.3 Possibility of hazardous reactions:**  
*Reacts with water and acids.*  
*Reacts with light alloys in the presence of moisture to form hydrogen.*
- **10.4 Conditions to avoid:** *No further relevant information available.*
- **10.5 Incompatible materials:** *No further relevant information available.*
- **10.6 Hazardous decomposition products:** *Hydrogen*

### **SECTION 11: Toxicological information**

- **11.1 Information on toxicological effects**
- **Acute toxicity** *Based on available data, the classification criteria are not met.*

· **LD/LC50 values relevant for classification:**

**1310-73-2 sodium hydroxide**

Oral LD50 2000 mg/kg (rat)

· **Primary irritant effect:**

· **On the skin:**

*Causes severe skin burns and eye damage.*

· **On the eyes:**

*Causes serious eye damage.*

· **Respiratory or skin sensitisation** *Based on available data, the classification criteria are not met.*

· **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**

· **Germ cell mutagenicity** *Based on available data, the classification criteria are not met.*

· **Carcinogenicity** *Based on available data, the classification criteria are not met.*

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

(Contd. of page 5)

### SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability:** No further relevant information available.
- **12.3 Bioaccumulative potential:** No further relevant information available.
- **12.4 Mobility in soil:** No further relevant information available.
- **Additional ecological information:**
- **General notes:**

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water.

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Must not reach sewage water or drainage ditch undiluted or unneutralised.

Throwing away bigger amounts into drains or aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. In the diluted product used, the pH-value is considerably reduced, so that after the use of the product the aqueous waste, emptied into drains, is only slightly polluting for water.

- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects:** No further relevant information available.

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation:**



Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

### SECTION 14: Transport information

- |                                       |                                |
|---------------------------------------|--------------------------------|
| · <b>14.1 UN-Number</b>               |                                |
| · <b>ADR, IMDG, IATA</b>              | UN1823                         |
| · <b>14.2 UN proper shipping name</b> |                                |
| · <b>ADR</b>                          | UN1823 SODIUM HYDROXIDE, SOLID |
| · <b>IMDG</b>                         | SODIUM HYDROXIDE, SOLID        |
| · <b>IATA</b>                         | Sodium hydroxide, solid        |

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

Contd. of page 6)

---

**· 14.3 Transport hazard class(es)**

· ADR



· **Class** 8 (C6) Corrosive substances.  
· **Label** 8

· IMDG, IATA



· **Class** 8 Corrosive substances.  
· **Label** 8

---

**· 14.4 Packing group**

· ADR, IMDG, IATA II

---

**· 14.5 Environmental hazards:**

· **Marine pollutant:** No

---

**· 14.6 Special precautions for user**

· **Danger code (Kemler):** Warning : Corrosive substances.  
80  
· **EMS Number:** F-A,S-B  
· **Segregation groups** Alkalis  
· **Stowage Category** A  
· **Segregation Code** SG35 Stow "separated from" acids.

---

**· 14.7 Transport in bulk according to Annex II of**

**Marpoland the IBC Code** Not applicable.

---

**· Transport/Additional information:**

· ADR

· **Limited quantities (LQ)** 1 kg  
· **Excepted quantities (EQ)** Code: E2  
Maximum net quantity per inner packaging: 30 g  
Maximum net quantity per outer packaging: 500 g  
· **Transport category** 2  
· **Tunnel restriction code** E


· IMDG

· **Limited quantities (LQ)** 1 kg  
· **Excepted quantities (EQ)** Code: E2  
Maximum net quantity per inner packaging: 30 g  
Maximum net quantity per outer packaging: 500 g

---

**· UN "Model Regulation":**

UN 1823 SODIUM HYDROXIDE, SOLID, 8, II

Contd. on page 8) 



*Safety data sheet*  
according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 20.06.2017

**Trade name: Eliminateur positif, bidon 1 Litre Ref: AR61**  
**Positive disposer, can 1 liter Ref: AR61**

(Contd. of page 7)

**SECTION 15: Regulatory information**

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**  
No further relevant information available.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

**SECTION 16: Other information**

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

**· Relevant phrases**

*H290 May be corrosive to metals.*

*H314 Causes severe skin burns and eye damage.*

**· Abbreviations and acronyms:**

*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*

*MDG: International Maritime Code for Dangerous Goods*

*ATA: International Air Transport Association*

*GH: Globally Harmonised System of Classification and Labelling of Chemicals*

*ENCS: European Inventory of Existing Commercial Chemical Substances*

*ELNCS: European List of Notified Chemical Substances*

*CAS: Chemical Abstracts Service (division of the American Chemical Society)*

*LC50: Lethal concentration, 50 percent*

*LD50: Lethal dose, 50 percent*

*PBT: Persistent, Bioaccumulative and Toxic*

*vPB: very Persistent and very Bioaccumulative*

*Met. Corr. 1: Corrosive to metals, Hazard Category 1*

*Skin Corr. 1A: Skin corrosion/irritation, Hazard Category 1A*

*Eye Dam 1: Serious eye damage/eye irritation, Hazard Category 1*