
Product datasheet

LINESTRA DIM 15 W/827 S14s

LEDinestra DIM | Tubular LED lamps



- Ideal for mirror lighting Hotels, restaurants Domestic applications Outdoor applications only in suitable luminaires

- Very long lifetime of up to 25,000 h Low energy consumption Good color rendering



Product datasheet

Technical data

Electrical data

Rated wattage	15.00 W
Nominal wattage	15.00 W
Nominal voltage	220...240 V
Operating frequency	50...60 Hz
Max. lamp no. on circuit break. 10 A (B)	100
Max. lamp no. on circuit break. 16 A (B)	200
Nominal current	0.073 A
Claimed equiv. conventional lamp power	75 W


Photometrical data

Rated color temperature	2700 K
Color rendering index Ra	≥80
Light color (designation)	Warm White
Standard deviation of color matching	≤6 sdc _m
Rated luminous flux	1055 lm
Nominal luminous flux	1055 lm
Color temperature	2700 K
Luminous flux	1055 lm
Lumen main.fact.at end of nom.life time	0.70

Light technical data

Beam angle	200 °
Starting time	< 0.5 s

Dimensions & weight



Overall length	1000 mm
----------------	---------

Product datasheet

Product weight	245.00 g
Length	1000 mm
Outer bulb	-
Diameter	29.0 mm

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
---------------------------	--------------

Lifespan

Nominal lamp life time	20000 h
Rated lamp life time	20000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	S14s
Mercury-free	Yes
Appropriate disposal acc. to WEEE	Yes
Mercury content	0.0 mg

Capabilities

Dimmable	Yes
----------	-----

Certificates & standards

Energy efficiency class	A
Energy consumption	15 kWh/1000h
Type of protection	IP20

Country specific categorizations

Order reference	LEDINESTRA 15W/
-----------------	-----------------

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075135604	LINESTRA DIM 15 W/827 S14s	Shipping carton box 5 Pieces Folding carton box	1060 mm x 270 mm x 75 mm	21.47 dm ³	2170.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

OSRAM is distribution partner
of LEDVANCE of LAMPS

OSRAM

OSRAM GmbH
Marcel-Breuer-Strasse 6
80807 Munich, Germany