


PRODUCT DATASHEET

PANEL PFM 600 UGR < 19 TPA 36 W 4000 K WT

PANEL PERFORMANCE 600 UGR<19 TPA | Square recessed panel luminaires with TP(A) rated diffuser, low glare, 600 x 600 mm



AREAS OF APPLICATION

- Direct replacement for luminaires with fluorescent lamps
- Offices, conference rooms
- Reception areas, foyers, corridors, elevators
- Suitable for recessed ceiling systems with grid size of 600 x 600 mm

PRODUCT BENEFITS

- Energy savings thanks to system efficacy of up to 110 lm/W
- Flexible application thanks to TP(A) rated diffuser for the UK market
- Good glare reduction (UGR < 19)
- Versions with DALI ECG available
- Emergency lighting possible with LEDVANCE Emergency Conversion Box
- Low flicker light thanks to special electronic control gear
- External driver for extended flexibility and easy installation
- Easy to clean thanks to a smooth diffuser
- 5 years guarantee

PRODUCT FEATURES

- Extruded aluminum frame
- Polycarbonate diffuser (TP(A) rated)
- Lifetime (L80/B10): up to 50,000 h (at 25 °C)



TECHNICAL DATA

Electrical data

Nominal wattage	36.00 W
Operating mode	External LED driver
Nominal voltage	220...240 V
Mains frequency	50/60 Hz
Power factor λ	≥ 0.95
Max. no. of lum. on circuit break. B16 A	19
Max. no. of lum. on circuit break. C10 A	19
Max. no. of lum. on circuit break. C16 A	30
Inrush current	23 A
Total harmonic distortion	$\leq 20\%$
Inrush current time T_{h50}	200 μ s


Photometrical data

Color temperature	4000 K
Color rendering index Ra	>80
Light color (designation)	Cool White
Luminous flux	3960 lm
Luminous efficacy	110 lm/W
Standard deviation of color matching	5 sdcM

Light technical data

Beam angle	90.00 °
UGR lateral	<19
UGR longitudinal	<19

Dimensions & weight



Length	595.0 mm
--------	----------

Width	595.0 mm
Height	34.0 mm
Product weight	1800.00 g
Mounting width	580.0 mm
Mounting length	580.0 mm

Colors & materials

Product color	White
Housing color	White
Body material	Aluminum
Light emitting surface material	Polycarbonate

Temperatures & operating conditions

Ambient temperature range	-10...+45 °C
----------------------------------	--------------

Lifespan

Number of switching cycles	25000
Lifespan L70/B50 at 25 °C	50000 h
Lifespan L80/B10 at 25 °C	50000 h
Lifespan L90/B10 at 25 °C	50000 h

Additional product data

Mounting type	Recessed/Suspended/Surface
Mounting location	Ceiling / Wall



Capabilities

Dimmable	No
Type of connection	Screwless terminal
LED module replaceable	Not replaceable

Certificates & standards



Type of protection	IP40
Protection class	II
Protection class IK (shock resistance)	IK02
Glow Wire Test according to IEC 60695-2-12	650 °C
Photobiological safety group EN62778	RG0
TP rating	TP(a)
Standards	CE/CB/RoHS

Light Distribution



LDC typ cone

LDC typ cone



LDC typ polar

LDC typ polar

EQUIPMENT / ACCESSORIES

- Accessories for several mounting options available
- External control gear included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075384309	Folding carton box 1	602 mm x 40 mm x 648 mm	2192.00 g	15.60 dm ³
4058075384316	Shipping carton box 4	667 mm x 182 mm x 634 mm	10015.00 g	76.96 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.