

## Features


Thermal strip gives great sharpness.

### FT-802



FT-802 can strip the insulation of AWG 38 wire with no nick.


Conventional wire stripper



Conventional wire stripper could make ragged edges of insulation or damage strands.

Due to the tweezers structure, the cutting edges are always aligned.

The blades can be securely fixed by making the frame with tweezers structure.



Output setting by the unit of 5%

Easy to set optimum output level as per material



Material	Output value (%)
PVC	10
PE	10
PA	20
PVDF	30
ETFE	40
SI	45
PTFE	55

\* The above values are for reference.


Blades are replaceable and a handpiece can be saved.

No need to replace a handpiece when blades get worn out. Blades can be easily replaced by using the hex-wrench (included in the unit) and the blade removal plate.

\* The blades must be cool before replacement for safety.



Remove blades.



Put removed blades in the holder.

### User-friendly display

Status of a handpiece at glance on the display.


User-friendly design for reduction of stress during the work.




- A handpiece is correctly set in a holder.
- Same as the output value.
- Ready to work immediately.
- Auto sleep function will activate after passing the set time.

## Optional Blades


### For FT-8004



G4-1601




G4-1602



G4-1603

### For FT-8003 (option)



G3-1601