## multicomp PRO

### RoHS Compliant

# Conductor : 1 Pair lapp screen Pure OFC copper 24AWG Stranding 28mm × 0.1mm Insulation : Material: XLPE Insulation Colour: Red & Blue Shield : Layer 1 Spiral lapp

	Construction 80mm × 0.1mm lapp pure OFC copper		
Jacket	: Material: Abrasion Resistant Matt PVC Compound Diameter: 6.35mm Jacket Colour: Blue		
Marking	: Blue : Evolution XPC OFC Professional Microphone Cable 301-001		
Reel lengths	: 100m / 500m Drum		
Weight	: 5.5 Kg/100m		

### Electrical Characteristics 20°C

Cable construction

Resistance	: 85Ω
Operating Temperature	: -20°C to +70°C
Capacitance (pF/m)	: 60 pF/m core to core
	110 pF/m core to screen

#### Part Number Table

Description	Part Number
Microphone Cable, 1 Pair, Blue, 100m	MP007901

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

