

PME271M622KR30

Aliases (P276CP224K275A)

PME271M/P276, Film, Metallized Paper, Safety, 0.22 uF, 10%, 275 VAC (X2), 630 VDC, 110°C, Lead Spacing = 20.3mm



Click [here](#) for the 3D model.

Dimensions

L	24mm MAX
H	16.5mm MAX
T	11.3mm MAX
S	20.3mm +/-0.4mm
LL	30mm +5mm
F	0.8mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	150

General Information

Series	PME271M/P276
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	No
Construction	Molded
Miscellaneous	SRF= 2.7 MHz.

Specifications

Capacitance	0.22 uF
Capacitance Tolerance	10%
Voltage AC	275 VAC (X2)
Voltage DC	630 VDC
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	600 V/us