



Mineral-insulated thermocouples to DIN 43 710 and EN 60 584

- for temperatures from -200 to +1200°C
- flexible sheath with shock-proof measuring insert
- protection tube diameter from 0.5mm
- fast response
- fitting length to suit application

Thanks to their special properties, mineral-insulated thermocouples are used in chemical plant, power stations, pipelines, in engine construction and on test beds. The thermocouple wires are embedded in compressed fire-resistant magnesium oxide inside the flexible thin-walled sheath.

The excellent heat transfer between the sheath and the thermocouple enables short response times ($t_{0.5}$ from 0.15sec) and high measurement accuracy. The shock-proof construction ensures a long life. The minimum bending radius is 5 x the external diameter. The minimum fitting length EL is 50mm for 0.5mm to 2.0mm dia., and 100mm for 3.0 to 6.0mm dia.

The thermocouples are normally insulated from the sheath. The measuring insert is fitted with thermocouples to EN 60 584 or DIN 43 710. Versions with two thermocouples are also available.

Test pressure: 40 bar (helium) leakage test at the measurement point.

Insulation resistance: thermocouple against sheath at ambient temperature for lengths up to 1m: 200M Ω , for lengths 1m and above: 200M Ω x m.



Technical data

Connection

available with cable ends as: bare wires, with ferrules, receptacles or multipole connector

Connecting cable

silicone, ambient temperature -50 to +180°C

PTFE, ambient temperature -190 to +260°C

metal braiding, ambient temperature -20 to +350°C

Protection tube

stainless steel 1.4541, thermocouple Type L and Type J

Inconel 2.4816 (Inconel 600), thermocouple Type K

Measuring insert

insulated assembly:

1 x Fe-Con J, EN 60 584, Cl. 2, operating temperature -200 to +800°C

1 x Fe-Con L, DIN 43 710, Cl. 2, operating temperature -200 to +800°C

1 x NiCr-Ni K, EN 60 584, Cl. 2, operating temperature -200 to +1200°C

2 x Fe-Con L, DIN 43 710, Cl. 2, operating temperature -200 to +800°C

2 x NiCr-Ni K, EN 60 584, Cl. 2, operating temperature -200 to +1200°C

Response times

in water with 0.4m/sec / in air with 2m/sec

0.5mm dia: water $t_{0.5}$ = 0.15sec, $t_{0.9}$ = 0.30sec / air $t_{0.5}$ = 3.5sec, $t_{0.9}$ = 8.0sec

1.0mm dia: water $t_{0.5}$ = 0.20sec, $t_{0.9}$ = 0.60sec / air $t_{0.5}$ = 7.5sec, $t_{0.9}$ = 17.0sec

1.5mm dia: water $t_{0.5}$ = 0.40sec, $t_{0.9}$ = 0.90sec / air $t_{0.5}$ = 10.0sec, $t_{0.9}$ = 25.0sec

2.0mm dia: water $t_{0.5}$ = 0.80sec, $t_{0.9}$ = 2.60sec / air $t_{0.5}$ = 13.0sec, $t_{0.9}$ = 34.0sec

3.0mm dia: water $t_{0.5}$ = 1.00sec, $t_{0.9}$ = 2.80sec / air $t_{0.5}$ = 22.0sec, $t_{0.9}$ = 64.0sec

4.5mm dia: water $t_{0.5}$ = 2.50sec, $t_{0.9}$ = 6.50sec / air $t_{0.5}$ = 34.0sec, $t_{0.9}$ = 113.0sec

6.0mm dia: water $t_{0.5}$ = 3.00sec, $t_{0.9}$ = 9.00sec / air $t_{0.5}$ = 55.0sec, $t_{0.9}$ = 170.0sec

JUMO GmbH & Co. KG

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

JUMO PROCESS CONTROL INC.

885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com

**Lead resistances in Ω/m at 20°C for mineral-insulated thermocouples**

Diameter D in mm	1 thermocouple resistance in Ω/m	2 thermocouples resistance in Ω/m
Thermocouple Fe-Con L		
6.0	0.66	0.85
4.5	1.40	1.80
3.0	2.70	3.50
2.0	5.00	7.70
1.5	12.00	-
1.0	21.50	-
Thermocouple Fe-Con J		
6.0	0.54	-
3.0	2.10	-
2.0	8.60	-
1.5	15.00	-
1.0	34.00	-
Thermocouple NiCr-Ni K		
6.0	0.88	2.70
4.5	1.56	4.80
3.0	3.50	11.00
2.0	7.90	25.00
1.5	14.00	-
1.0	32.00	-
0.5	126.00	-


Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk


885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com




Dimensions




Type 901221/10



Type 901221/20



Type 901221/3x



Type 901221/40

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com



Order details: Mineral-insulated thermocouples to DIN 43 710 and EN 60 584

(1) Basic version

901221/10 Mineral-insulated thermocouple with bare connecting wires



901221/20 Mineral-insulated thermocouple with standard flat emf-free connector



(2) Measuring insert / operating temperature in °C

x	x	1040	1 x Fe-Con J, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
x	x	1042	1 x Fe-Con L, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
x	x	1043	1 x NiCr-Ni K, operating temperature -200 to +1200°C, sheath, Mat. Ref. 2.4816
x	x	2042	2 x Fe-Con L, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
x	x	2043	2 x NiCr-Ni K, operating temperature -200 to +1200°C, sheath, Mat. Ref. 2.4816

(3) Protection tube diameter D in mm

x	x	0.5	0.5mm, only with Type 1 x NiCr-Ni K
x	x	1	1mm
x	x	1.5	1.5mm
x	x	2	2mm
x	x	3	3mm
x	x	4.5	4.5mm
x	x	6	6mm

(4) Fitting length EL in mm (50 ≤ EL ≤ 50000)

x	x	100	100mm
x	x	200	200mm
x	x	300	300mm
x	x	400	400mm
x	x	500	500mm
x	x	...	please specify in plain text (50mm steps)

(5) Extra codes

x	x	000	no extra code
x	x	309	uninsulated assembly (thermocouple welded to tip)

Order code (1) (2) (3) (4) (5) ,...

Order example 901221/10 - 1042 - 3 - 200 / 000¹

1. List extra codes in sequence, separated by commas.

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com



Order details: Mineral-insulated thermocouples to DIN 43 710 and EN 60 584

(1) Basic version

901221/32	Mineral-insulated thermocouple with siliconized compensating cable	
901221/33	Mineral-insulated thermocouple with PTFE- insulated compensating cable	
901221/34	Mineral-insulated thermocouple and compensating cable with metal-braiding and glass silk insulation	

(2) Measuring insert / operating temperature in °C

x x x	1040	1 x Fe-Con J, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
x x x	1042	1 x Fe-Con L, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
x x x	1043	1 x NiCr-Ni K, operating temperature -200 to +1200°C, sheath, Mat. Ref. 2.4816
x x	2042	2 x Fe-Con L, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
x x	2043	2 x NiCr-Ni K, operating temperature -200 to +1200°C, sheath, Mat. Ref. 2.4816

(3) Protection tube diameter D in mm

x x x	0.5	0.5mm, only with Type 1 x NiCr-Ni K
x x x	1	1mm
x x x	1.5	1.5mm
x x x	2	2mm
x x x	3	3mm
x x x	4.5	4.5mm
x x x	6	6mm

(4) Fitting length EL in mm (50 ≤ EL ≤ 50000)

x x x	100	100mm
x x x	200	200mm
x x x	300	300mm
x x x	400	400mm
x x x	500	500mm
x x x	...	please specify in plain text (50mm steps)

(5) Compensating cable end

x x x	03	bare cable ends
x x x	11	ferrules to DIN 46 228 Part 4 (standard)
x x x	13	receptacle 6.3 to DIN 46 247
x x x	80	multipole connector (please specify type in plain text)

(6) Compensating cable length AL in mm (500 ≤ AL ≤ 500000)

x x x	2500	2500mm (standard)
x x x	...	please specify in plain text (500mm steps)

(7) Extra codes

x x x	000	no extra code
x x x	309	uninsulated assembly (thermocouple welded to tip)
x x x	317	shielded compensating cable

Order code (1) - (2) - (3) - (4) - (5) - (6) / (7)
Order example 901221/32 - 1042 - 3 - 200 - 11 - 2500 / 000¹

1. List extra codes in sequence, separated by commas.

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk


885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com



Order details: Mineral-insulated thermocouples to DIN 43 710 and EN 60 584

(1) Basic version

901221/40 Mineral-insulated thermocouple with terminal head Form J



(2) Measuring insert / operating temperature in °C

- x 1040 1 x Fe-Con J, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
- x 1042 1 x Fe-Con L, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
- x 1043 1 x NiCr-Ni K, operating temperature -200 to +1200°C, sheath, Mat. Ref. 2.4816
- x 2042 2 x Fe-Con L, operating temperature -200 to +800°C, sheath, Mat. Ref. 1.4541
- x 2043 2 x NiCr-Ni K, operating temperature -200 to +1200°C, sheath, Mat. Ref. 2.4816

(3) Protection tube diameter D in mm

- x 3 3mm
- x 4.5 4.5mm
- x 6 6mm

(4) Fitting length EL in mm (50 ≤ EL ≤ 50000)

- x 100 100mm
- x 200 200mm
- x 300 300mm
- x 400 400mm
- x 500 500mm
- x ... please specify in plain text (50mm steps)

(5) Process connection

- x 103 thread 3/8" pipe
- x 104 thread 1/2" pipe

(6) Extra codes

- x 000 no extra code
- x 309 uninsulated assembly (thermocouple welded to tip)

Order code (1) (2) (3) (4) (5) (6) ,...

Order example 901221/40 - 1042 - 6 - 200 - 104 / 000¹

1. List extra codes in sequence, separated by commas.

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com



Stock versions:

(1)	(2)	(3)	(4)	(5)	Sales No.
901221/20	1043	3	100	000	90/00056899
901221/20	1043	3	250	000	90/00068440

Stock versions:

(1)	(2)	(3)	(4)	(5)	(6)	(7)	Sales No.
901221/32	1042	6	100	11	2500	000	90/00049206
901221/32	1042	6	200	11	2500	000	90/00068450
901221/32	1042	6	500	11	2500	000	90/00068452
901221/32	1042	3	100	11	2500	000	90/00056809
901221/32	1042	3	200	11	2500	000	90/00068433
901221/32	1042	3	300	11	2500	000	90/00068434
901221/32	1042	3	500	11	2500	000	90/00068435
901221/32	1042	1.5	100	11	2500	000	90/00056811
901221/32	1042	1.5	200	11	2500	000	90/00068438
901221/32	1042	1.5	500	11	2500	000	90/00068439
901221/32	1043	6	100	11	2500	000	90/00056812
901221/32	1043	6	200	11	2500	000	90/00068427
901221/32	1043	6	300	11	2500	000	90/00068428
901221/32	1043	6	500	11	2500	000	90/00068429
901221/32	1043	3	100	11	2500	000	90/00056813
901221/32	1043	3	200	11	2500	000	90/00068441
901221/32	1043	3	300	11	2500	000	90/00068442
901221/32	1043	3	500	11	2500	000	90/00068443
901221/32	1043	1.5	100	11	2500	000	90/00049205
901221/32	1043	1.5	200	11	2500	000	90/00068436
901221/32	1043	1.5	500	11	2500	000	90/00068437
901221/32	1043	0.5	100	11	2500	000	90/00066345

Stock versions:

(1)	(2)	(3)	(4)	(5)	(6)	Sales No.
901221/40	1042	6	100	104	000	90/00087482
901221/40	1042	6	300	104	000	90/00068454
901221/40	1043	6	100	104	000	90/00087483
901221/40	1043	6	200	104	000	90/00068430
901221/40	1043	6	300	104	000	90/00068431
901221/40	1043	6	500	104	000	90/00068432