




## MA500-1A - MA500-3A Adjustable Torque Screwdrivers with Window Scale and ESD Safe









### PRODUCT DETAILS

- Over-torque limiting clutch
- Single scale in cN.m
- Range covering between 10 cN.m and 450 cN.m torque values
- Torque measurement clockwise only, can be used to loosen fasteners without affecting the internal mechanism
- Accurate to  $\pm 6\%$  CW
- Clicking system triggers a tactile and audible signal
- 1/4" hex non-magnetic spring-loaded bit holder to avoid damaging sensitive equipment or components in electronic applications
- All-metal 3-lobe handle
- Easy to operate
- Easy-read scale
- Lindström's torque screwdrivers offer comfort with a User-friendly shape and non-slip grip
- Ideal choice for flexible applications as well as volume production
- Supplied in an adjustable semi-transparent square tube
- Supplied with a factory declaration of conformity in compliance with international standards
- Standards: ISO 6789/IEC61340-5-1
- ESD safe (IEC 61340-5-1 and EN 100015-1)
- Made in USA









PRODUCT ATTRIBUTES







Product: **MA500-1A**

	16-80 cNM		20-200 in·oz		
	1/4 in		1 cNM	<b>A</b>	138 mm
<b>A</b>	5.43 in	<b>B</b>	18,2 mm	<b>B</b>	0,72 in
<b>C</b>	28 mm	<b>C</b>	1.10 in	<b>D</b>	9,6 mm
<b>D</b>	0,38 in		0.2 kg		

Product: **MA500-2A**

	40-200 cNM				3-15 lb·in
	1/4 in		2 cNM	<b>A</b>	157 mm
<b>A</b>	6.18 in	<b>B</b>	18,2 mm	<b>B</b>	0,72 in
<b>C</b>	28 mm	<b>C</b>	1.10 in	<b>D</b>	9,6 mm
<b>D</b>	0,38 in		0.26 kg		

Product: **MA500-3A**

	90-450 cNM				5-40 lb·in
	1/4 in		5 cNM	<b>A</b>	171 mm
<b>A</b>	6.73 in	<b>B</b>	18,2 mm	<b>B</b>	0,72 in
<b>C</b>	32 mm	<b>C</b>	1.26 in	<b>D</b>	9,6 mm
<b>D</b>	0,38 in		0.308 kg		