

HARDCASE® PROFESSIONAL® PIVOTPLUS

HCSW21

For the most demanding tasks, look no further than the *Energizer®* *HARDCASE®* *PROFESSIONAL®* *PIVOTPLUS*. With tool-quality construction and advanced LED technology, this light is designed to meet even the most challenging jobs. Constructed with Professionals in mind, it withstands drop after drop, off a ladder or even a two-story building. Designed with a 175 degrees pivoting function plus a versatile magnetic base, this light provides the flexibility needed for any project. The large push button switch can be easily operated while wearing gloves, while adjustable light modes let the user decide the balance of brightness and runtime. In addition, this light is water resistant for those rainy, outdoor tasks.



Provides
300
Lumens of
Light



Provides
Run Time
of 5 hours



Shines Light
on objects up
to 30 Meters
Away



Sustains 7
Meter
Drop Test.



Water Resistant
IPX4 – works after
splashing water
on all sides

DESIGN BENEFITS

- ✓ Pivoting head rotates up to 175 degrees
- ✓ Exceptionally durable
- ✓ Survives drop after drop from a two-story building
- ✓ Weather-resistant
- ✓ Built-in lanyard slot
- ✓ Large switch for easy operation
- ✓ 20 Year Designed to Last based on typical consumer usage patterns

LIGHT AND POWER SOURCE

- ✓ Features Advanced LED Technology
- ✓ Operates on 2 AA batteries

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power:
Power consumption 3.3W / Batteries AA
Energizer E91 3.0V dc
LED Specifications: LED 3.0V cc / 1100 mA

CERTIFICATES AND COMPLIANCE



EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards



Results based on: Energizer® MAX® Alkaline / E91

PERFORMANCE BENEFITS

- ✓ Bright, uniform beam is ideal for projects
- ✓ Adjustable beam output for extended runtime
- ✓ Dimmable – Press and hold to select output
- ✓ Magnetic base to secure light on metal surfaces

SPECIFICATIONS

Weight Excluding Batteries:

140 grams / 4.9 Ounces

Dimensions:

180mm x 50 mm x 45mm / 7" x 2" x 1.8"

NUMBER OF OPERATING MODES: 2

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m)
High	300	5h	30
Low	30	30	10

Before using your flashlight, please read all instructions and cautionary marking on the package and the light.

This datasheet contains information specific to products manufactured at the time publication. Contents do not constitute a claim or warranty.

©2018 Energizer