



Sensors > Position Sensors > Liquid Level Switches > Horizontal Liquid Level Switches



Liquid Level Switch Mounting: **Side Entry**

Medium/Liquid: **Alcohol, Fuel, Oil**

Contact Form: **A**

Fitting: **1/2 NPT**

Liquid Level Switch Material: **Glass Filled Nylon 6.6**

[All Horizontal Liquid Level Switches \(20\)](#)

Features

Product Type Features

Float SG	.85
----------	-----

Body Features

Liquid Level Switch Mounting	Side Entry
Liquid Level Switch Material	Glass Filled Nylon 6.6

Contact Features

Contact Form	A
--------------	---

Dimensions

Liquid Level Switch Cable Length	.5 m[1.64 ft]
----------------------------------	---------------

Other

Medium/Liquid	Alcohol, Fuel, Oil
Fitting	1/2 NPT

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | MEAS LS



Customers Also Bought



TE Part #1-2273088-3
M12 x 1.0 angled plug pigtail A



TE Part #152871
14-12 PIDG R/T 1/4 STUD WHITE



TE Part #152873
14-12 PIDG NYLON RT NO 8 WHITE



TE Part #1-1703648-1
HEAVY DUTY SEALED CONNECTOR HOUSINGS



TE Part #1011-027-0805
CLIP, PA66, GRY, 5.08MM HOLE, ST, DT8PIN



TE Part #1472914002
RNF-3000-18/6-1-SP



TE Part #1241150-7
7P MOD II BREAK AWAY HDR, SMD, BLISTER



TE Part #1-1623705-2
CPG1206 10K 1% 50PPM



TE Part #EB1046-000
CPGI-CWT-9002-BULK

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_80052-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_80052-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_80052-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LS_SERIES](#)

English