

FLUKE



Fluke i5sPQ3, 5 A AC Current Clamps, 3-pack

Key features

- Low level current clamp measures up to 5 A AC
- Compact shape makes transporting and storing convenient; the clamp measures only 116 x 43 x 23 mm (4.6 x 1.7 x .9 in)
- Take accurate readings without breaking the circuit
- CAT III 600 V (For insulated conductors only)

Product overview: Fluke i5sPQ3, 5 A AC Current Clamps, 3-pack

A pack of 3 pieces of the i5s current clamps, specially configured to provide low current accuracy while taking measurements on secondary current transformers. This cost-saving 3-pack is perfect for use with 3-phase tools such as the Fluke 434 or Fluke 435. The compact shape makes transporting and storing convenient. Takes accurate readings without breaking the circuit.

Specifications: Fluke i5sPQ3, 5 A AC Current Clamps, 3-pack

Specifications		
Nominal current range	5 A	
Continuous current range	10 mA to 6 A	
Maximum non-destructive current	70 A	
Lowest measurable current	10 mA	
Basic accuracy		48 Hz to 65 Hz
	10 mA to 1 A	1% + 5 mA
	1 A to 5 A	1%
Useable frequency	40 Hz to 5 kHz	
Output level(s)	400 mV/A	
Input load impedance	> 1 MΩ in parallel with up to 47 pF	
Crest factor	≤ 3, add 0.7% to accuracy	
Safety specifications		
Safety	CAT III 600 V per IEC/EN61010-1, Pollution Degree 2	

Maximum voltage	600 V AC
Mechanical and General Specifications	
Warranty	1 year
Maximum conductor diameter	15 mm
Output cable length	2.5 m
BNC adapter	Yes
BNC to banana adapter included	No