



DEUTSCH | DEUTSCH Common Contact

TE Internal #: 0462-209-16141

DEUTSCH Common Contact, Automotive Terminals, Socket, Pin Diameter 1.59 mm [.063 in], Terminal Transmits 0 – 24 A (Low Power), 14AWG Wire Size

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals > DEUTSCH SOLID CONTACTS



Terminal & Splice Type: **Socket**

Mating Pin Diameter: **1.59 mm [.063 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **2 mm²**

[All DEUTSCH SOLID CONTACTS \(44\)](#)

Features

Product Type Features

Sealable	No
Primary Locking Feature	On the Terminal
Automotive Terminal Wire Type	Copper

Contact Features

Typical Current Rating	13 A
Crimp Type	Indent
Terminal & Splice Type	Socket
Mating Pin Diameter	1.59 mm [.063 in]
Automotive Terminal Interface Plating	Nickel (Ni)
Contact Termination Area Plating Material	Nickel (Ni)

Termination Features

Automotive Terminal Termination Method	Crimp
--	-------

Dimensions

Wire Size	2 mm ²
Wire Size Search	14 AWG

Usage Conditions

Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C,
-----------------------------	--



120 °C, 125 °C[176 °F][185 °F][194 °F][212 °F]
[221 °F][230 °F][248 °F][257 °F]

Operating Temperature Range

-55 – 125 °C[-67 – 257 °F]

Packaging Features

Packaging Method

Carton

Packaging Quantity

2500

Other

Customer Preferred Contact

Yes

Terminal Transmits

0 – 24 A (Low Power)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUL 2021
(219)
Candidate List Declared Against: JAN 2021
(211)
SVHC > Threshold:
Pb (.7% in Component Part)
Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-ST273
DEUTSCH SOLID CONTACTS



TE Part # CAT-ST858-CH8172
DEUTSCH STRIKE HOUSINGS



TE Part # JS-16-00
JIFFY SPLICE, Size 16



TE Part # HDT-48-00
CRIMP TOOL, HAND




TE Part # HDT-50-00
CRIMP TOOL



TE Part # 2372208-1
SDE HDT-1561-NG DEUTSCH 16-20AWG ASSY



TE Part # CAT-D487-CH8172
DEUTSCH DT Series Housings & Connectors



TE Part # CAT-D781-CH8172
DEUTSCH DRB HOUSINGS



TE Part # CAT-D799-CH8172
DEUTSCH DRC HOUSINGS



TE Part # CAT-H3910-CH8172
DEUTSCH HD10 HOUSINGS



TE Part # CAT-H3930-CH8172
DEUTSCH HD30 HOUSINGS



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 HOUSINGS



TE Part # CAT-D487-DCH8172
DEUTSCH DT DETECTOR CONNECTOR



TE Part # CAT-D48-SFT273
DEUTSCH STAMPED & FORMED CONTACTS



TE Part # HDFB-16-06S
MODULE, FEEDBACK, 21P, BLK, SZ16, SOC




TE Part # HDP-400
POWER CRIMPER



TE Part # HDP26-24-14SN-L015
PLG, 14P, BLK, N, THD, 4/12/16, S



TE Part # DTV06-18SC
PLG, 18P, GRN, N, C




TE Part # DT16-18SA-K004
PLG, 18P, BLK, E, A



TE Part # DT16-18SE-K004
PLG, 18P, BLK, E, E

Also in the Series | **DEUTSCH Common Contact**



Automotive Terminals(95)



Insertion & Extraction Tools(8)

Customers Also Bought

TE Part #0460-215-16141
DEUTSCH SOLID CONTACTSTE Part #0411-240-2005
EXT TOOL, SIZE 20, 16-22 AWG, N,
REDTE Part #W6S
WEDGE LOCK, 6P, PLG, ORG, STD,
DTTE Part #2411-001-2405
PANEL NUT, SIZE 24, HDPTE Part #0413-204-2005
DEUTSCH SEALING PLUGS

Documents

Product Drawings

SOC, SOLID, SIZE 16, 14AWG, NI

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_0462-209-16141_99_c-0462-209-16141-99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_0462-209-16141_99_c-0462-209-16141-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_0462-209-16141_99_c-0462-209-16141-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Engineering Report](#)

English

Product Environmental Compliance

[MD_0462-209-16141_0716201863_dmtec](#)

English

[MD_0462-209-16141_0716201863_dmtec](#)

English