


## PCB MOUNTING LEDs - Ø 3mm Up to 8 units may be integrated in 1 6.3 2.3 4.6 array with a rugged tie bar Multi-colour permutations 0.5Sq Reverse polarity options 5.0 Anode --- (Red Bi-colour) 113-120 SERIES Dimensions in mm (Typical) MLQ = 50LEDs

## Ordering Information & Typical Technical Characteristics (Ta = 25°C)

Mean Time Between Failure = 100,000 Hours. Low Current Models 250,000 Hours. Luminous intensity figures refer to the unmodified discrete LED.

110 000 01	Reu/Green	Willie Dilluseu	2.0/2.2	20	20/20				
113-330-04	Red/Green	White Diffused	2.0/2.2*	20	25/25	625/565			
113-314-04	Green		2.2*	20	20	565			
113-311-04	Yellow		2.1*	20	20	590	]		
113-305-04	Red 🔴	Coloured Diffused	2.0*	20	35	625	Wide	-40 ~ +80	-40 ~ +80
113-314-01	Green		2.2	2	20	565			
113-311-01	Yellow		2.1	2	20	590			
113-305-01	Red 🔴		2.0	2	35	625			
			S <sup>-</sup>	TANDARD	INTENSITY				
Part Number	COLOUR	LENS	VOLTAGE DC Vopr	CURRENT DC lopr	LUMINOUS INTENSITY Iv@20mA	WAVE LENGTH p	VIEWING ANGLE	OPERATING TEMP Topr	STORAGE TEMP Tstg



<sup>\* =</sup> Voltage DC for 20mA product is Vf@20mA, not Vopr

LEAD CROPPING OPTION, SEE PAGE 23