



# Product data sheet

## Power tools for trade & industry

Cordless Combi

### GSB 12V-35



Perfect balance between compactness, productivity and performance

#### The most important data

Max. drilling diameter in masonry	10 mm
Max. screw diameter	8 mm
Weight excl. battery	0.8 kg

**Part Number** 0 601 9J9 002[> More product information](#)

## Technical data

### Technical data

Torque (soft/hard/max.)	20/35/- Nm
No-load speed (1st gear / 2nd gear)	0 – 460 / 0 – 1,750 rpm
Battery type	Lithium-ion
Max. impact rate	26,250 bpm
Chuck capacity, min./max.	0.8 / 10 mm
Weight excl. battery	0.8 kg
Torque settings	20+1
Tool dimensions (height)	160 mm
Packaging dimensions (width x length x height)	226 x 334 x 105 mm
Clamping range, min.	0.8 mm
Clamping range, max.	10 mm
Weight incl. battery	1 kg

### 'Total vibration values (Drilling in metal)'

Vibration emission value ah	0 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### 'Total vibration values (Impact drilling in masonry)'

Vibration emission value ah	14.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### 'Total vibration values (Screwdriving)'

Vibration emission value ah	0 m/s <sup>2</sup>
-----------------------------	--------------------

Uncertainty K	1.5 m/s <sup>2</sup>
---------------	----------------------

### Drilling diameter

Max. drilling diameter in wood	32 mm
Max. drilling diameter in steel	10 mm
Max. drilling diameter in masonry	10 mm

### Screw diameter

Max. screw diameter	8 mm
---------------------	------

## Noise/vibration information

### Drilling in metal

Vibration emission value ah	0 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Impact drilling in masonry

Vibration emission value ah	14.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Screwdriving

Vibration emission value ah	0 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

## Advantages:

- Highest impact rate in the 12V category, enabling powerful impact drilling of up to Ø10 mm in masonry
- Compact design allows perfect handling and easy operation – even in challenging working situations
- High rotation speed of 1,750 rpm for a broad variety of jobs

