



D-CT

TE Internal #: EL8088-000

D-CT, Printable Tubing, Continuous Printable Tubing Type, Fluid Resistant Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE FLUID RESISTANT D-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Fluid Resistant**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **White**

Supplied Inner Diameter: **19 mm [ .75 in ]**

[All CONTINUOUS TUBE FLUID RESISTANT D-CT \(16\)](#)

**Features**

**Product Type Features**

Printable Tubing Type	Continuous
Printable Tubing Grade	Fluid Resistant

**Body Features**

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White

**Dimensions**

Supplied Inner Diameter	19 mm[.75 in]
Recovered Inside Diameter	6.4 mm[.25 in]
Compatible Cable Diameter Range	6.4 – 15.2 mm[.25 – .598 in]

**Usage Conditions**

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

**Operation/Application**

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

**Printer/Label Features**

Recommended Printer	See TE Document 411-121005 the Printer
---------------------	--



Product Ribbon Matrix

Printer Technology Thermal Transfer

Packaging Features

Packaging Quantity 50

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006  
 Current ECHA Candidate List: JUL 2021 (219)  
 Candidate List Declared Against: JUL 2021 (219)  
 Does not contain REACH SVHC

Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # CP8122-000  
T6112DS-PRINTER




TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

### Also in the Series | D-CT




Printable Tubing(16)

### Customers Also Bought




TE Part #F26167-000  
HX-SCE-1K-6.4-50-S1-4



TE Part #5068004001  
CGPT-38/19-9-SP



TE Part #6787634001  
ZH-100-3/8-0-SP



TE Part #5038814001  
DCPT-10/5-45-SP



TE Part #176819-000  
B-150-11



TE Part #270225-000  
B-150-07



TE Part #4-1768018-2  
EET-1325P-4

### Documents

[Product Drawings](#)  
[D-CT-50M-18-OUT-9](#)

English

[D-CT-50M-18-OUT-9](#)

English

[Datasheets & Catalog Pages](#)



## D-CT, Continuous Diesel Resistant Heat Shrinkable Identification Tube

English

---

### Product Specifications

Product Specification

English

---

### Instruction Sheets

Instruction Sheet (non U.S.)

English