



# Product data sheet

Power tools for trade & industry

Cordless Drill/Driver

## GSR 18V-55



Bosch's powerful entry-level 18 V drill driver with brushless motor

### The most important data

|                         |            |
|-------------------------|------------|
| Max. screw diameter     | 10 mm      |
| Weight excl. battery    | 1 kg       |
| Torque (soft/hard/max.) | 28/55/- Nm |

**Part Number** 0 601 9H5 202

[> More product information](#)

## Technical data

### Technical data

|                                     |                         |
|-------------------------------------|-------------------------|
| Torque (soft/hard/max.)             | 28/55/- Nm              |
| No-load speed (1st gear / 2nd gear) | 0 – 460 / 0 – 1,800 rpm |
| Battery type                        | Lithium-ion             |
| Chuck capacity, min./max.           | 1.5 / 13 mm             |
| Weight excl. battery                | 1 kg                    |
| Torque settings                     | 20+1                    |

### 'Total vibration values (Drilling in metal)'

|                             |                      |
|-----------------------------|----------------------|
| Vibration emission value ah | 2 m/s <sup>2</sup>   |
| Uncertainty K               | 1.5 m/s <sup>2</sup> |

### Drilling diameter

|                                 |       |
|---------------------------------|-------|
| Max. drilling diameter in wood  | 35 mm |
| Max. drilling diameter in steel | 13 mm |

### Screw diameter

|                     |       |
|---------------------|-------|
| Max. screw diameter | 10 mm |
|---------------------|-------|

## Noise/vibration information

### Drilling in metal

|                             |                      |
|-----------------------------|----------------------|
| Vibration emission value ah | 2 m/s <sup>2</sup>   |
| Uncertainty K               | 1.5 m/s <sup>2</sup> |



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Tough and powerful: high performance of 55 Nm and 1,750 RPM ensures maximum efficiency for work in wood and metal
- Robust 13-mm Roehm metal chuck offers ideal power transfer for drilling and screwdriving
- Features brushless motor for extended tool lifetime and longer battery runtimes

