



CONNECTIVITY

WiFi Built-in WiFi

Ethernet - Yes

Bluetooth - Yes

Connections - HDMI 1.4 x 1

- Component input x 1

- Composite input x 1

- USB 2.0 x 1

Audio output - Optical x 1

- RCA x 1

TUNER

TV tuner - Freeview HD

- FreeSat

Electronic programme guide - EPG and 7-day catch up with Freeview Play

AUDIO

Speakers - 2

Audio power - 10 W

Sound enhancement - Virtual surround

FEATURES

Motion control - Yes

Voice control - Via remote

VESA mount - 75 x 75

Table-top stand - Yes

Other features - Sleep timer

- Parental lock

ENERGY CONSUMPTION

Energy efficiency class - A

On-mode power consumption - 25 W

Annual power consumption - 36 kWh

Product Specification



Model
24TN510S

SCREEN

Screen size - 24"

Screen technology - LED backlit

Resolution - HD Ready 1366 x 768p

Bezel width - Left / right / top: 18.5 mm
- Bottom: 19.6 mm

PICTURE QUALITY

Motion rate - 50 Hz

Contrast - Peak brightness: 200 nits

Native contrast ratio - 1000:1

Dynamic contrast ratio - 5,000,000:1

Noise reduction - Yes

SMART

Smart platform - webOS 4.5

Smart TV services - Catch up TV: BBC iPlayer,
ITV Hub, All 4, My5

Streaming - Netflix, Prime Video, NOW TV

App store - LG Content Store

Full internet browser

Social media - YouTube

Gaming apps

Screen mirroring - Android

Smartphone app - LG TV Plus

Other smart features - Home IoT

GENERAL

Colour - Black

Material - Plastic

Internal menu languages - 39 languages

Box contents - LG 24TN510S 24" Smart LED TV

- Remote control

- Remote battery

DIMENSIONS

TV with stand - 393.8 x 563.1 x 148.6 mm (H x W x D)

TV - 340.9 x 563.1 x 58 mm (H x W x D)

Boxed - 402 x 700 x 142 mm (H x W x D)

WEIGHT

TV - 3.25 kg

TV with stand - 3.6 kg

Boxed: 4.8 kg