

2134441-2 ✓ ACTIVE


TE Internal #: 2134441-2

USB Connectors, B, 2.0, Micro Profile, Receptacle, 1 Port, Mid Mount, Reverse Right Angle, Tape & Reel, Offset, Surface Mount

[View on TE.com >](#)



Connectors > Audio & Video Connectors > USB Connectors



USB Connector Type: **B**

USB Version: **2.0**

Connector Profile: **Micro**

Connector & Housing Type: **Receptacle**

Number of Ports: **1**

Features

Product Type Features

Integral Locking Latch	Without
USB Connector Type	B
USB Version	2.0
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Connector
LED	Without

Configuration Features

Number of Ports	1
Number of Positions	5

Body Features

Offset	.88 mm
Shell Plating Finish	Matte
Connector Profile	Micro



Shell Plating Material	Tin over Nickel
------------------------	-----------------

Contact Features

Contact Current Rating (Max)	1.8 A
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	.76 μm [29.52 μin]

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Locking Feature	Without
Locating Posts	Without
PCB Mount Location	Mid Mount
PCB Connector Seating	Offset
PCB Mount Retention Type	Hold-Down
Connector Mounting Type	Board Mount

Housing Features

Body Orientation	Reverse Right Angle
Centerline (Pitch)	.65 mm[.025 in]
Housing Material	Thermoplastic
Housing Color	Black

Dimensions

Tail Length	.7 mm[.028 in]
PCB Thickness (Recommended)	.8 – 1. mm[.031 – .039 in]

Usage Conditions

Soldering Temperature (Max)	260 °C[500 °F]
Mating Cycles (Max)	10000
Operating Temperature Range	-30 – 85 °C[-22 – 185 °F]

Operation/Application

Halogen Free	No
Assembly Process Feature	Without Pick and Place Cover
Circuit Application	Power & Signal

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---



Industry Standard	USB 2.0
-------------------	---------

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Packaging Quantity	1000
--------------------	------

Other

Comment	Reverse Type
---------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Reflow solder capable to 260°C
---------------------------	--------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1735446-3
2MM PITCH HPI POST HEADER,
VERTICAL, 3P



TE Part #D70981-000
VERSAFIT-MINI-SPL-3/32-BK



TE Part #104351-1
02 MODII HDR DRST B/A W/HD



TE Part #1447009-5
SHIELD FINGER 0820 TYPE



TE Part #1-1825137-5
A103SYCB04




TE Part #1-1825137-6
A103SYCQ04



TE Part #1-2176326-4
CRGP 0603 120R 1%



TE Part #1-1735413-1
Assembly Slimline SATA Receptacle
7P+6P



TE Part #1571625-1
TACT,6X6,SMT,J-LEAD,50GF

Documents

Product Drawings

MICRO USB, TYPE B, MIDMOUNT, REVERSE

Japanese

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2134441-2_A_c-2134441-2-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2134441-2_A_c-2134441-2-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2134441-2_A_c-2134441-2-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[5-1773464-3_Quick_Reference_Guide_Micro_USB_Connectors](#)

English

Product Specifications

[Product Specification](#)

Japanese

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

Japanese