



### TECHNICAL INFORMATION

Watts:	45
Lumens:	3600
Shape:	Square
Input Power:	AC:200-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Aluminium + PMMA + PP
PF:	>0.9
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	120°
Color Temperature:	3000K
Dimension:	595x595x14mm
Output Voltage:	DC:30-42V

### 60X60 PANELS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 6028 - 1567 940

[View more details](#)



### FEATURES

- Powerful LED light source with lumen efficiency of 80 LM/W LM/W
- Strong and sturdy Aluminium + PMMA + PP body
- Fitted with high efficiency SMD LED Chips
- Easy to connect driver for quicker installation
- Compatible driver SKU 6614(Not Included)
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

CE/EMC

CE/LVD



### PACKAGING

Gross Weight (Kgs): 2.9  
Unit CBM: 0.009309896  
Dimension: 595x595x14mm

### MASTER BOX PACKAGING

Box Qty: 6  
Qty Per Pallet: 114  
Length (Box) mm: 610  
Width (Box) mm: 20  
Height (Box) mm: 600

### LISTING DETAILS

Commodity Code: 9405109890  
Ean Code: 3800157650847