

VOXTAKER 100

Large-diaphragm Studio Microphone with Cardioid Polar Pattern

Professional condenser microphone featuring true condenser capsule with cardioid polar pattern. It can be used with confidence in a variety of professional applications, such as recording studios, broadcasting, podcasting, and stage performances. With its gold-plated diaphragm capsule and premium FET preamp circuitry, VoxTaker 100 has very low self-noise and high output, to reproduce even the subtle sound and fulfil the requirement of high sound quality for broadcasting and recording. The package includes Shock-Mount and Pop Filter, all inside a plastic case.

€ 102,00

including VAT



KEY FEATURES

34mm Gold-Plated Pressure Gradient Transducer

Cardioid Polar Pattern

High Quality FET Preamp Stage

High Absorption Shock-mount

Stylish and Innovative Pop Filter

Plastic Case

MORE SPECIFICATIONS

Element	34mm pressure gradient capsule
---------	--------------------------------

Cardioid Polar Pattern	
------------------------	--

Frequency Response	30Hz - 20kHz
--------------------	--------------

Sensitivity	-38dB (0dB = 1V/Pa at 1kHz)
-------------	-----------------------------

Output Impedance	150 (at 1kHz)
------------------	---------------

Load Impedance	1000 ohms
----------------	-----------

Self-Noise	16dB A-weighted
------------	-----------------

Max Input SPL	130dB (@ 1kHz - 1% T.H.D.)
---------------	----------------------------

S/N Ratio	78dB
-----------	------

Microphone Size (WxHxD)	188x50x50 mm
-------------------------	--------------

Microphone Weight	272 g
-------------------	-------

Case Size (WxHxD)	340 x 280 x 90 mm
-------------------	-------------------

Package Weight (Mic., case and accessories)	1.5kg
---	-------