FLOW METER PROCESS OMEGA CONTROL INFORMATION SYSTEMS

FLR Series



FLR Flow Sensors

- ✓ 2% FS Accuracy
- ✓ No Straight Pipe Run Required
- ✓ Mounts in Any Position
- 4 to 20 mA,0 to 5 Vdc, and0 to 10 VdcStandard Outputs
- Digital Flow Rate and Total Flow Indicator
- ✓ In-Field Compensation for:
 - Specific Gravity of All Fluids
 - Viscosity of Petroleum-Based Fluids
 - Specific Gravity,
 Pressure, and
 Temperature of
 Pneumatic Applications



Rugged In-Line Flow Sensors

Available in 13 mm (½"), 19 mm (¾"), and 32 mm (1½") sizes with anodized aluminum or brass. Comes with 4.5 m (15') of stripped end integral cable. In the field, integral cable can be extended up to 300 m (1000') with shielded copper cable. Units are securely

protected in a sturdy cast aluminum enclosure, and are easy to install and mount in any position, vertical or horizontal. Capable of monitoring fluids to 150 GPM or pneumatic lines to 1000 SCFM.

SPECIFICATIONS

Temperature Range:
-29 to 116°C (-20 to 240°F)

Maximum Pressure: 3500 psig (liquids); 1000 psig (gases)

Power Requirement:

0 to 5 Vdc Output: 10 to 30 Vdc @

0.75 W maximum

0 to 10 Vdc Output: 12 to 30 Vdc @

0.75 W maximum

4 to 20 mA Output: Loop-powered,

30 Vdc maximum

Power Consumption: 25 mA maximum

Circuit Protection:

Reverse polarity and current limit

Repeatability: ±0.5% Non-Linearity: ±0.05%

Isolation: Inherently isolated from

the piping system

Display: Fixed or toggle modes of operation for rate and totalizer display. 8-digit, 0.70" high numeric display for rate and total 8-digit 0.35" high alphanumeric display for units

and setup

Response Time: 1.0 sec Temperature Drift:

0.05% of span per °C maximum

Analog Outputs:

4 to 20 mA into $1K\Omega$ maximum 0 to 5 Vdc into $10K\Omega$ minimum 0 to 10 Vdc into $10K\Omega$ minimum

User Connections: 15' pig-tail (standard)

Transmission Distance:

4 to 20 mA limited by cable resistance 0 to 5 Vdc 300 m (1000') maximum 0 to 10 Vdc 300 m (1000') maximum

Enclosure:

Material: Anodized and epoxy powder-coated aluminum with

polycarbonate lens

Seals: Silicone gasket between enclosure and lens/cover FKM O-rings between enclosure and

flow meter body

Connection: 4-pin connection

(standard)

Fasteners: T303 SS

Rating: NEMA 12 and 13 (IP52/54)

Materials:

2024 - T351 anodized aluminum body, piston and cone C360 brass body, piston and cone petroleum (oil)

common parts

Spider Plate: T316 SS Spring: T302 SS Fasteners: T303 SS Pressure Seals: FKM Lens: Polycarbonate

Retaining Ring: SAE 1070/1090

carbon steel

Retaining Spring: SAE 1070/1090

carbon steel

Internal Magnet: PPS/ceramic Enclosure Seal: Silicone gasket


water-based, water, air

common parts
Spider Plate: T316 SS

Spider Plate: 1316 SS
Spring: T302 SS
Fasteners: T303 SS
Pressure Seals: FKM
Lens: Polycarbonate
Retaining Ring: T316 SS
Retaining Spring: ST316 SS
Internal Magnet: PPS/ceramic
Enclosure Seal: Silicone gasket

Dimensions: mm (inch)

| | В | С | D | E | F | G | Н | I | J | K |
|-------------------------------|---------|---------|---------|--------|--------|--------|--------|--------|--------|-----------|
| Nominal Port Size | Length | Length | Length | Width | Width | Width | Width | Depth | Offset | Hole Dia. |
| (SAE 6) | 168 | 134 | 163 | 152 | 82 | 76 | 107 | 75 | 38 | 8 |
| | (6.60) | (5.27) | (6.41) | (6.00) | (3.23) | (3.00) | (4.20) | (2.94) | (1.51) | (0.31) |
| (SAE 6) | 168 | 134 | 163 | 152 | 82 | 76 | 107 | 75 | 38 | 8 |
| | (6.60) | (5.27) | (6.41) | (6.00) | (3.23) | (3.00) | (4.20) | (2.94) | (1.51) | (0.31) |
| ³ / ₄ | 183 | 134 | 179 | 152 | 91 | 76 | 107 | 75 | 32 | 8 |
| (SAE 6) | (7.20) | (5.27) | (7.04) | (6.00) | (3.60) | (3.00) | (4.20) | (2.94) | (1.27) | (0.31) |
| 1 | 183 | 134 | 179 | 152 | 91 | 76 | 107 | 75 | 32 | 8 |
| (SAE 6) | (7.20) | (5.27) | (7.04) | (6.00) | (3.60) | (3.00) | (4.20) | (2.94) | (1.27) | (0.31) |
| 1 ¹ / ₄ | 310 | 271 | 296 | 194 | 123 | 97 | 128 | 114 | 56 | 8 |
| (SAE 6) | (12.20) | (10.68) | (11.65) | (7.63) | (4.84) | (3.82) | (5.02) | (4.50) | (2.20) | (0.31) |
| 1½ | 310 | 271 | 296 | 194 | 123 | 97 | 128 | 114 | 56 | 8 |
| (SAE 6) | (12.20) | (10.68) | (11.65) | (7.63) | (4.84) | (3.82) | (5.02) | (4.50) | (2.20) | (0.31) |





| To Order | | | | |
|-----------|------------------|-------------|------|----------|
| Model No. | Flow Range | Medium | NPT | Body |
| FLR6102D | 0.2 to 2.0 GPM | Oil | 1/2 | Aluminum |
| FLR6105D | 0.5 to 5.0 GPM | Oil | 1/2 | Aluminum |
| FLR6115D | 1 to 15 GPM | Oil | 1/2 | Aluminum |
| FLR7120D | 0.2 to 2.0 GPM | Oil | 3/4 | Aluminum |
| FLR7130D | 3 to 30 GPM | Oil | 3/4 | Aluminum |
| FLR8140D | 4 to 40 GPM | Oil | 1 | Aluminum |
| FLR8150D | 5 to 50 GPM | Oil | 1 | Aluminum |
| FLR9175D | 10 to 75 GPM | Oil | 11/4 | Aluminum |
| FLR9110D | 10 to 100 GPM | Oil | 11/4 | Aluminum |
| FLR9115D | 10 to 150 GPM | Oil | 11/4 | Aluminum |
| FLR6302D | 0.2 to 2.0 GPM | Water | 1/2 | Brass |
| FLR6305D | 0.5 to 5.0 GPM | Water | 1/2 | Brass |
| FLR6315D | 1 to 15 GPM | Water | 1/2 | Brass |
| FLR7320D | 2 to 20 GPM | Water | 3/4 | Brass |
| FLR7330D | 3 to 30 GPM | Water | 3/4 | Brass |
| FLR8340D | 4 to 40 GPM | Water | 1 | Brass |
| FLR8350D | 5 to 50 GPM | Water | 1 | Brass |
| FLR9375D | 10 to 75 GPM | Water | 11/4 | Brass |
| FLR9310D | 10 to 100 GPM | Water | 11/4 | Brass |
| FLR9315D | 10 to 150 GPM | Water | 11/4 | Brass |
| FLR6725D | 2 to 25 SCFM | Air 100 psi | 1/2 | Aluminum |
| FLR6750D | 5 to 50 SCFM | Air 100 psi | 1/2 | Aluminum |
| FLR7710D | 10 to 100 SCFM | Air 100 psi | 3/4 | Aluminum |
| FLR7715D | 15 to 150 SCFM | Air 100 psi | 3/4 | Aluminum |
| FLR8725D | 25 to 250 SCFM | Air 100 psi | 1 | Aluminum |
| FLR9740D | 25 to 400 SCFM | Air 100 psi | 11/4 | Aluminum |
| FLR9760D | 50 to 600 SCFM | Air 100 psi | 11/4 | Aluminum |
| FLR9710D | 100 to 1000 SCFM | Air 100 psi | 11/4 | Aluminum |

Comes complete with operator's manual.

For 5-point NIST certificate add "-NIST5" to model number for additional cost.

For British standard pipe thread parallel add "-BSPP" to model number, no additional cost.

Ordering Examples: FLR6105D, flow transmitter, 0.5 to 5.0 GPM for oil, with analog output FLR5101D, flow transmitter, 0.1 to 1.0 GPM for oil with analog output.