

## DK U-F DK5 0-10V

**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

### Similar to illustration



#### MCZ: The smallest solution

- The smallest analogue signal converter in terminal block format on the market
- Space-saving conversion of analogue signals in the control cabinet thanks to the slim, 6 mm wide module width
- Simple wiring with plug-in cross-connectors

#### General ordering data

Version	DC/f transformer, Input : Frequency, 0...1/ 4/ 8/ 16 kHz
Order No.	<a href="#">8242040000</a>
Type	DK U-F DK5 0-10V
GTIN (EAN)	4008 19040 1979
Qty.	10 pc(s).

Creation date July 23, 2021 8:25:51 AM CEST

Catalogue status 16.07.2021 / We reserve the right to make technical changes.

## DK U-F DK5 0-10V

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	64 mm	Height (inches)	2.52 inch
Width	12 mm	Width (inches)	0.472 inch
Length	76.8 mm	Length (inches)	3.024 inch
Net weight	22.1 g		

## Temperatures

Storage temperature	-25 °C...60 °C	Operating temperature	0 °C...50 °C
---------------------	----------------	-----------------------	--------------

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Input

Input resistance, voltage	100 kΩ	Input voltage	0...10 V
Number of inputs	1		

## Output

Number of outputs	1	Output current	20 mA
Output frequency	0...1/ 4/ 8/ 16 kHz	Output level	PNP, Ub-0.7 V
Status indicator	LED, pulsing		

## General data

Accuracy	0.2 % v. FSR	Current consumption	14 mA without load
Galvanic isolation	2-way isolator	Input/Output	DC/ f
Rail	TS 35, TS 32	Temperature coefficient	≤ 250 ppm/K
Type of connection	Screw connection	Voltage supply	24 V DC ± 10 %

## Insulation coordination

Galvanic isolation	2-way isolator	Insulation voltage	1 kV DC
Insulation voltage input or output/rail	4 kV <sub>eff</sub>	Rated voltage	300 V

## Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	4 mm <sup>2</sup>

## Classifications

ETIM 6.0	EC002918	ETIM 7.0	EC002918
ETIM 8.0	EC002918	ECLASS 9.0	27-21-01-28
ECLASS 9.1	27-21-01-28	ECLASS 10.0	27-21-01-28
ECLASS 11.0	27-21-01-28		

**Data sheet****DK U-F DK5 0-10V****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**Approval/Certificate/Document of  
Conformity[Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)