



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

| | |
|----------------------------|-------|
| Applicator & Product Style | OCEAN |
|----------------------------|-------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2151027-7

[OC-042F062O-CRIMPTOOLINGKIT](#)

Customers Also Bought



TE Part #102387-9

[40 MODIV HSG COMP DR .100 POL](#)



TE Part #2-1633730-4

[CRIMPER, WIRE F .062 F](#)



TE Part #2-1633730-7

[CRIMPER, WIRE F .042F](#)




TE Part #1-480351-2

[01P CMNL CAP HSG RED](#)



TE Part #1241980-8

[SPECIAL STANDARD TIMER HOUSING 8POS](#)



TE Part #1855118-1

[U POD .187 STRAIGHT SAPR090F140F LM & G](#)



TE Part #121397P013

[ES2000-NO.3-B8-0-41MM](#)



TE Part #938365P003

[VERSAFIT-1/8-0-0.6IN-ST](#)



TE Part #1-455888-2

[SPACER, CRIMPER\(\(060\)](#)



TE Part #1320928-4

[STRIP GUIDE](#)

Documents

- Datasheets & Catalog Pages

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English
- Instruction Sheets

[Instruction Sheet \(U.S.\)](#)



English