



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 11

TEROSON MS 9220 BK

SDS No. : 634057
V003.0

Revision: 24.09.2021
printing date: 25.09.2021

Replaces version from: 05.05.2021

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

TEROSON MS 9220 BK

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
MS Sealant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Adhesives
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000
Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information

Safety data sheet available on request.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Sealant

Base substances of preparation:

Silane-modified polyether

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	258-207-9 01-2119537297-32	0,1- < 1 %	Repr. 2 H361f Eye Dam. 1 H318 Aquatic Chronic 2 H411 Aquatic Acute 1 H400

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures**

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

All common extinguishing agents are suitable.

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In case of fire toxic gases can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Temperatures between + 10 °C and + 25 °C

7.3. Specific end use(s)

MS Sealant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [Dust, inhalable dust]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [Dust, respirable dust]		4	Time Weighted Average (TWA):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		3,5	Time Weighted Average (TWA):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		7	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		3,5	Time Weighted Average (TWA):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		7	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE]		10	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [DUSTS NON-SPECIFIC]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [DUSTS NON-SPECIFIC]		10	Time Weighted Average (TWA):		IR_OEL
Carbon black 1333-86-4 [CARBON BLACK]		3	Time Weighted Average (TWA):		IR_OEL
Carbon black 1333-86-4 [CARBON BLACK]		3	Time Weighted Average (TWA):		IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	aqua (freshwater)		0,018 mg/l				
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	aqua (marine water)		0,0018 mg/l				
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	aqua (intermittent releases)		0,007 mg/l				
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	sediment (freshwater)				29 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	sediment (marine water)				2,9 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Soil				5,9 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	sewage treatment plant (STP)		1 mg/l				

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Workers	dermal	Long term exposure - systemic effects		1,8 mg/kg	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Workers	Inhalation	Long term exposure - systemic effects		1,27 mg/m ³	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	General population	Inhalation	Long term exposure - systemic effects		0,31 mg/m ³	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	General population	dermal	Long term exposure - systemic effects		0,9 mg/kg	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	General population	oral	Long term exposure - systemic effects		0,18 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure good ventilation/suction at the workplace.

Hand protection:

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR; ≥ 1 mm thickness) or natural rubber (NR; ≥ 1 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR; ≥ 1 mm thickness) or natural rubber (NR; ≥ 1 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Protective goggles

Protective eye equipment should conform to EN166.

Skin protection:

Wear protective equipment.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

Use only personal protection that's CE-labelled according to Directive 89/686/EEC (Europe) or to Regulation No. 819 of 19 August 1994 (Norway).

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste pasty black
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	Not applicable, Mixture reacts with water.
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	> 93 °C (> 199.4 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	1,4 g/cm ³
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative)	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

No decomposition if used according to specifications.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	LD50	3.700 mg/kg	rat	OECD Guideline 423 (Acute Oral toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	LD50	> 3.170 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	not irritating	24 h	rabbit	EPA OPP 81-5 (Acute Dermal Irritation)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	corrosive	24 h	rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)

Carcinogenicity

No data available.

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	NOAEL P 109 mg/kg NOAEL F1 121 mg/kg	two-generation study	oral: feed	rat	OECD Guideline 443 (Extended One-Generation Reproductive Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	NOAEL 36 mg/kg	oral: feed	daily	rat	other guideline:

Aspiration hazard:

No data available.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	LC50	4,4 mg/l	96 h	Lepomis macrochirus	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC50	8,58 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	NOEC	0,23 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC50	0,705 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC10	0,188 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC50	> 100 mg/l	3 h	activated sludge, domestic	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	not readily biodegradable.	aerobic	24 %	28 d	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	0,35	25 °C	OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

In consultation with the responsible local authority, must be subjected to special treatment.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

08 04 10 Waste adhesives and sealants other than those mentioned in 08 04 09.

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	dioctyltin oxide CAS 870-08-6
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable
VOC content (2010/75/EU)	0 %

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H318 Causes serious eye damage.
- H361f Suspected of damaging fertility.
- H400 Very toxic to aquatic life.
- H411 Toxic to aquatic life with long lasting effects.

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.