

PRODUCT-DETAILS

OTP63B4M

OTP63B4M Enclosed Switch Disconnecter



General Information

Extended Product Type	OTP63B4M
Product ID	1SCA022401R4910
EAN	6417019131344
Catalog Description	OTP63B4M Enclosed Switch Disconnecter

Long Description

The enclosure in the OTP series is using a rigid glass reinforced polycarbonate enclosure. The enclosure is UV protected, protected against low-pressure water jets (IP65), and hence built for outdoor and indoor use. The cable entries are threaded and have knock out holes for 2 parallel cables and one control cable, both from top and bottom. The handle is padlockable and made for three padlocks. The cover is interlocked. The interlocking can be by-passed, for thermographing etc. The switch is made for 5 wire system, and have a fixed neutral terminal and PE terminal.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Country of Origin	Finland (FI)

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
-----------------------------------	-----------------

Instructions and Manuals

1SCC340002M0012

Mechanical Drawings

OTPK201490SM32.stp

Dimensions

Product Net Width	145 mm
Product Net Height	200 mm
Product Net Depth / Length	90 mm
Product Net Weight	0.9 kg

Technical

Rated Operational Current AC-21A (I_e)	(500 V) 80 A (380 ... 415 V) 80 A (690 V) 80 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 80 A (690 V) 80 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 75 A (500 V) 58 A (690 V) 20 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 37 kW (500 V) 37 kW (690 V) 18.5 kW
Conventional Thermal Current (I_{the})	Fully Enclosed 80 A
Rated Impulse Withstand Voltage (U_{imp})	1.5 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 750 V
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V AC) 2.1 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 1.5 kA
Power Loss	at Rated Operating Conditions per Pole 4.5 W
Pollution Degree	3
Handle Color	Black
Handle Type	Selector handle
Position of Line Terminals	Top In - Bottom Out
Standards	IEC 60947-1, -3
Number of Poles	4
Connecting Capacity Main Circuit	Screw Clamp 1.5...35 mm ² Screw Clamp / PE Terminal 2pcs, 1.5...35 mm ²
Cable Entry Position	Up/Down
Cable Outlets Per Side	2xM32+M16 / 2xM32+M16
Degree of Protection	acc. to IEC 60529 IP65
Impact Resistance Rating	Housing IK08
Enclosure Material	Plastic
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC

Mounted Auxiliary Contacts	0 NO, 0 NC
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	0
Position of Neutral Terminals	Top In - Bottom Out
Position of PE Terminals	Top In - Bottom Out

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

BV Certificate	1SCC340018D0204
Declaration of Conformity - CE	1SCC340003D2704
DNV GL Certificate	1SCC340045D0204
Instructions and Manuals	1SCC340002M0012
RoHS Information	1SCC340034D0203

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	162 mm
Package Level 1 Depth / Length	222 mm
Package Level 1 Height	148 mm
Package Level 1 Gross Weight	1 kg
Package Level 1 EAN	6417019131344

Classifications

Object Classification Code	Q
ETIM 5	EC000216 - Switch disconnecter
ETIM 6	EC000216 - Switch disconnecter
ETIM 7	EC000216 - Switch disconnecter
UNSPSC	39122233
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Switch-Disconnectors → Enclosed Switch-Disconnectors

