

HOT APPLICATIONS

STRONGOTHERM TERRY BROWN



434X X23XXX



Nylon, polyester, cotton terry cloth glove, ambidextrous, knitted wrist. The all-round protection against contact heat up to 250 degrees as well as cut risks. Very price competitive.

KNITTED GLOVES

art.no.	sizes
STR50	7S, 8M, 9L, 10XL
Standards	EN420, EN388, EN407, irreversible risk
CE Category	Intermediate design
Packaging	12 pairs per polybag, 72 pairs per case

STRONGOTHERM HEAVYWEIGHT



124X X24X 234X X34X (only for STR124H)



32oz heavyweight loop pile cotton thermal resistant gloves. Cut and sewn with knitted wrist and canvas or terry cloth cuff in 2 lengths and also as mitt. Heavyweight design for ultimate thermal protection. Ideal for contact heat protection up to 250°C.

art.no.	description	size
STR100H	knitted wrist	10XL
STR103H	canvas cuff, length 30 cm (12")	10XL
STR105H	canvas cuff, length 40 cm (16")	10XL
STR121H	terry cloth cuff, length 25 cm (10")	10XL
STR104H	terry cloth cuff, length 30 cm (12")	10XL
STR124H	terry cloth cuff, length 40 cm (16")	10XL
Standards	EN420, EN388, EN407, CE Category: Intermediate design	
Packaging	STR100H & STR 121H: 12 pairs per bag, 144 pairs per case	
	STR103-STR124H: 12 pairs per bag, 72 pairs per case	

STRONGOTHERM LIGHTWEIGHT MITT



124X X14X

24oz lightweight loop pile cotton thermal resistant gloves. Cut and sewn with knitted wrist. Lightweight design for thermal protection and increased flexibility. Ideal for contact heat protection up to 100°C.

Fingerless mitt available (STR128L).



art.no.	size
STR100L	10XL
STR128L	10XL
Standards	EN420, EN388, EN407
CE Category	Intermediate design
Packaging	12 pairs per bag, 144 pairs per case

STRONGOTHERM LIGHTWEIGHT SLEEVES



124X X14XXX



24oz lightweight loop pile cotton thermal resistant sleeve. Cut and sewn sleeve with knitted wrist and elasticated arm section. Length 38 and 50 cm. Lightweight design for thermal protection and increased flexibility. Ideal for contact heat protection up to 100°C.

art.no.	description
STR2235L	length 38 cm (15")
STR2240L	length 50 cm (20")
Standards	EN420, EN388, EN407
CE Category	Intermediate design
Packaging	6 pairs per bag, 48 pairs per case

GRIP N HOT MILL



134X X241XX

Seamless knitted glove with a double layer of cotton and acrylic yarns. Brown N Nitrile pattern on both sides for excellent grip, ambidextrous.



Heavyweight design for ultimate thermal protection. Ideal for contact heat protection up to 250°C.

art.no.	size
51/7146	10XL
Standards	EN420, EN388, EN407
Packaging	12 pairs per polybag, 72 pairs per case

GRIP N KEVLAR HOT MILL



144X X241

Seamless knitted, plated Kevlar, double ply, with brown Nitril N coating on both sides. Heat protection up to 250°C.



art.no.	size
52/7456	10XL
Standards	EN 420, EN388, EN407
CE Category	Intermediate risk
Packaging	12 pairs per bag, 144 pairs per case

KEVLAR PLUS HOT MILL



254X 434XX

Seamless knitted Kevlar gloves, inside with cotton lining for a heat protection up to 350°C. Furthermore excellent protection against cut,



used for handling hot parts like taking metal sheets out of ovens.

art.no.	description	size
62/8434	length 34cm (13")	10XL
Standards	EN420, EN 388, EN 407	
CE Category	Intermediate design	
Packaging	6 pairs per bag, 72 pairs per case	