DIN RAIL TEMPERATURE TRANSMITTER

SEM213 P DIN RAIL RTD TRANSMITTER

- PT100 (3 types), Ni100, Ni120, Cu100, ohms (10 to 400Ω)
- SIMPLE PUSH BUTTON CONFIGURATION
 - ADVANCED USER CONFIG FOR ACCESS TO 56 PRE SET TEMPERATURE RANGES
- USER PUSH BUTTON TRIM
- PROGRAMMABLE BURNOUT



The SEM213/P is a cost effective "smart" DIN rail mount transmitter that accepts resistance temperature sensors and converts sensor output over a configured range to a standard industrial (4 to 20) mA transmission signal.

A simple push button operation allows the user to select RTD type, Burnout direction, Select fixed ranges and trim 4 and 20 mA points.

The SEM213P transmitter incorporates the latest digital technology to ensure accurate drift free performance.

If required the desired range can be specified at the time of order, removing the need for user configuration. If the range is not specified then the transmitter will be supplied at the default range of (0 to 100) $^{\circ}$ C type Pt100 IEC.

PUSH BUTTON CONFIGURATION

User Range

Two levels of configuration are available to the user, the first level user range, allows the user to re-range the transmitter.

This level is available under normal use and operates in a similar manner to the SEM203P Product. The user can identify the input type set by counting the number of program led flashes on power up. The input type cannot be changed at this level of configuration.

Advanced User Configuration

In this level the single push button and two LED indicators are used and allow the user to navigate through a series of five menus, allowing full configuration of the transmitter. The menus are as follow:-

Menu 1	Select Input type		
Menu 2	Select either user configured range or select one of seven (per input) fixed ranges		
Menu 3	Select burnout direction		
Menu 4	Trim output current \circledast either 4 mA or 20 mA.		
Menu 5	Reset to factory default and clear user trim		

SPECIFICATIONS @ 20 ° C

INPUT

Sensor	Range (°C)	Accuracy	
Pt100 IEC 0.003851	-200 to 850		
Pt100 IPTS-68 0.00391	200 1 620		
Pt100 IPTS-68 0.00392	-200 to 630		
Ni 100 DIN 0.00618	-60 to 180	± 0.2°C + (±0.05% of rdg)	
Ni 120 0.00672			
Cu 100 0.00427	-80 to 260		
Cu 53	-50 to 180		
	Range (Ohms)		
Ω	10 to 400	±0.01% FSR	

Sensor Burnout

Either up or down scale output

Stability

RTD ± 0.005% FSR/°C Ohms ± 0.025 % FSR / °C



DIN RAIL TEMPERATURE TRANSMITTER

OUTPUT	
Output Type 2 wire (4 to 20) mA current lo	ор
Output range 4.0 mA to 20.0 mA	
Output Connection Screw Terminal	
Maximum output 21.5 mA(in high burnout	
condition)	
Minimum output 3.8 mA (in low burnout	
condition)	
Accuracy (mA output / 2000) or 5 uA	
(Which ever is the greater)	
Loop Voltage effect ± 0.2 uA / V	
Thermal drift ± 1 uA / °C Typically ± 1.5 uA	
Maximum output load [(Vsupply-10)/20] K Ohms	
(Example 700 ohms @ 24 V)	

Fixed Ranges

Range	Inputs Pt100	Input Ni100 Cu53	Inputs Ni120 Cu100	Input Ω
Ra	(°C)	(°C)	(°C)	Ω
1	User	User	User	User
2	0 to 50	0 to 50	0 to 50	0 to 50
3	0 to 100	0 to 100	0 to 100	0 to 100
4	0 to 150	0 to 150	0 to 150	0 to 150
5	0 to 200	0 to 180	0 to 260	0 to 200
6	-20 to 30	-20 to 30	-20 to 30	0 to 250
7	-30 to 70	-30 to 70	-30 to 70	0 to 300
8	-100 to 100	-100 to 100	-100 to 100	0 to 400

GENERAL SPECIFICATION Update time

500 mS 1 second 4 Seconds (Output < 4 mA during start up) 1 minute to full accuracy 10 to 30 Volts dc

60 mm x 75 mm x 12.5 mm

Electrical equipment for

ENVIRONMENTAL

Response Time

Start up time

Warm-up time

Power Supply

(-20 to +70) °C Ambient operating range Ambient storage temperature (-50 to +90) °C Ambient humidity range (10 to 90) % RH non condensing

45 g

PHYSICAL Dimensions

Weight

APPROVALS

- EMC BS EN 61326 :1998 -
- measurement control and laboratory use. ANNEX A Immunity test requirements for equipment intended for use in industrial locations ANNEX F Test configurations, operational conditions and performance criteria for transducers with integrated or remote signal


IEC 61000-4-2 Electrostatic discharge IEC 61000-4-3 EM Field IEC 61000-4-4 Transient Burst (output) IEC 61000-4-5 Surge (output)

Note - Sensor input wires to be less than 30 metres to comply.

conditioning.

Status Instruments Ltd Green Lane Business Park Green Lane, Tewkesbury Gloucestershire, UK GL20 8DE

Tel: +44 (0)1684 296818 Fax: +44 (0)1684 293746 Email: sales@status.co.uk Website: www.status.co.uk D2477-01-01 SEM213P DATA SHEET



ORDER CODE: SEM 213P

