9070T500D2

Transformer, Type T, industrial control, 500 VA, 240/480 VAC primary / 24 VAC secondary, 1 phase, 50/60 Hz, 115 °C rise





Main

Product Type	Industrial Control Transformer
Power Rating	500 VA
Туре	Т

Complementary

Complementary		
Number of Phases	1 phase	
Power Rating	500 VA UL	
	500 VA CSA	
	500 VA NOM	
	300 VA	
Temperature Rise	115 °C	
Electrical Connection	Screw clamp terminals	
Height	3.84 in (97.54 mm)	
Width	4.5 in (114.30 mm)	
Depth	5.49 in (139.45 mm)	
Material	Copper winding	
Fingersafe Cover Compatibility	FSC2	

Environment

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

0 11 0		
Category	16201 - 9070 T (NOT TF) 250-2000VA	
Discount Schedule	CP8	
GTIN	00785901845447	
Nbr. of units in pkg.	1	
Package weight(Lbs)	11.9 lb(US) (5.40 kg)	
Returnability	Yes	
Country of origin	MX	

Packing Units

Package 1 Height	6.50 in (16.510 cm)	
Package 1 width	6.80 in (17.272 cm)	
Package 1 Length	7.50 in (19.050 cm)	

Offer Sustainability


Sustainable offer status	Green Premium product	
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
EU RoHS Directive	Compliant EPEU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	₽¥Yes	
China RoHS Regulation	[©] China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
PVC free	Yes	

Contractual warranty

Warranty	10 Years
----------	----------

9070T500D2

Approximate Dimensions



9070T500D2

Connections and Wiring Diagrams

Voltage and Connection Options

Voltage Code	Voltages		Connections	
	Primary	Secondary	Primary	Secondary
D2	240 x 480	24	240: Connect to H1 and H4 Jumper H1 with H3 Jumper H2 with H4 480: Connect to H1 and H4 Jumper H2 with H3	
D23	120 x 240	24	120: Connect to H1 and H4 Jumper H1 with H3 Jumper H2 with H4 240: Connect to H1 and H4 Jumper H2 with H3	- Connect to X1 and X2
D89	115 x 230	24	115: Connect to H1 and H4 Jumper H1 with H3 Jumper H2 with H4 230: Connect to H1 and H4 Jumper H2 with H3	
D92	230 x 460	24	230: Connect to H1 and H4 Jumper H1 with H3 Jumper H2 with H4 460: Connect to H1 and H4 Jumper H2 with H3	

